

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296056

Luminaire Tested: P3AS13R25W2N902750DE010 E3DLD1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296056
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25W2N902750DE010 E3DLD1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 614.0 lumens
Efficiency: N/A
Efficacy: 49.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296056
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296056

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.0	9.8
10°-20°	143.8	23.4
20°-30°	162.4	26.5
30°-40°	128.5	20.9
40°-50°	64.9	10.6
50°-60°	26.0	4.2
60°-70°	16.6	2.7
70°-80°	9.2	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	366.2	59.6
0°-40°	494.7	80.6
0°-60°	585.6	95.4
0°-90°	614.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	614.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	666	
5°	647	60
15°	518	144
25°	355	162
35°	206	128
45°	81	65
55°	27	26
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1296056

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	665.5
1°	665.5
2°	663.2
3°	659.4
4°	654.0
5°	647.1
6°	638.7
7°	628.8
8°	618.1
9°	605.8
10°	592.8
11°	578.3
12°	564.5
13°	548.4
14°	533.1
15°	517.8
17.5°	475.0
20°	432.9
22.5°	393.2
25°	354.9
27.5°	317.4
30°	279.2
32.5°	243.2
35°	205.8
37.5°	171.3
40°	138.4
42.5°	107.9
45°	81.1
47.5°	60.4
50°	43.6
52.5°	32.9
55°	26.8
57.5°	24.5
60°	21.4
62.5°	19.1
65°	16.8
67.5°	14.5
70°	12.2
72.5°	10.7
75°	8.4
77.5°	6.9
80°	5.4
82.5°	3.8
85°	2.3
87.5°	0.8



TEST NUMBER: P1296056
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1WMH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)