

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296094

Luminaire Tested: P3AS13R25W2N902750DE010 E3PH1MW\_5000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296094  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902750DE010 E3PH1MW\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,  
E3PH1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 820.0 lumens  
Efficiency: N/A  
Efficacy: 66.7 lumens/watt  
Spacing Criteria (0/90/45): 0.36 / 0.36 / 0.36  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296094  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3PH1MW\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296094

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3PH1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	99	99	98	98	98
2	113	109	107	105	111	108	105	103	105	103	101	102	100	99	99	98	97	99	98	97	96
3	110	106	103	100	108	104	102	99	102	100	98	100	98	96	98	96	95	98	96	95	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	96	95	93	92
5	105	100	96	94	103	99	96	93	97	95	93	96	94	92	95	93	91	95	93	91	90
6	102	97	94	91	101	97	93	91	95	93	91	94	92	90	93	91	89	93	91	89	89
7	100	95	92	89	99	95	91	89	94	91	89	93	90	88	92	89	88	92	89	88	87
8	98	93	90	87	98	93	89	87	92	89	87	91	88	87	90	88	86	90	88	86	85
9	97	91	88	86	96	91	88	85	90	87	85	89	87	85	89	86	85	89	86	85	84
10	95	89	86	84	94	89	86	84	88	86	84	88	85	83	87	85	83	87	85	83	83

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1254154
5°	1071140
10°	675316
15°	314304
20°	64709
25°	13210
30°	2811
35°	589
40°	315
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1296094

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3PH1MW\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	405.5	49.5
10°-20°	376.7	45.9
20°-30°	35.6	4.3
30°-40°	2.1	0.3
40°-50°	0.1	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	817.8	99.7
0°-40°	819.9	100.0
0°-60°	820.0	100.0
0°-90°	820.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	820.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5719	
5°	4866	406
15°	1384	377
25°	55	36
35°	2	2
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1296094  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3PH1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5719.4
2.5°	5506.6
5°	4866.2
7.5°	4000.8
10°	3032.9
12.5°	2190.8
15°	1384.5
17.5°	669.4
20°	277.3
22.5°	110.3
25°	54.6
27.5°	25.6
30°	11.1
32.5°	4.5
35°	2.2
37.5°	1.1
40°	1.1
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)