

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294134

Luminaire Tested: P3AS09R55W2N902750DE010 E3DL1GPH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294134  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R55W2N902750DE010 E3DL1GPH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 314.0 lumens  
Efficiency: N/A  
Efficacy: 34.9 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294134  
CATALOG NUMBER: P3AS09R55W2N902750DE010 E3DL1GPH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1294134

CATALOG NUMBER: P3AS09R55W2N902750DE010 E3DL1GPH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	86221
5°	85340
10°	82430
15°	76187
20°	65736
25°	51922
30°	36841
35°	23744
40°	14255
45°	8032
50°	4332
55°	1529
60°	1403
65°	1349
70°	1282
75°	1186
80°	1137
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8032 cd/sqm



TEST NUMBER: P1294134

CATALOG NUMBER: P3AS09R55W2N902750DE010 E3DL1GPH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	36.5	11.6
10°-20°	92.8	29.6
20°-30°	97.3	31.0
30°-40°	56.7	18.1
40°-50°	21.2	6.8
50°-60°	5.0	1.6
60°-70°	2.6	0.8
70°-80°	1.5	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	226.5	72.1
0°-40°	283.3	90.2
0°-60°	309.5	98.6
0°-90°	314.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	314.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	393	
5°	388	36
15°	336	93
25°	215	97
35°	89	57
45°	26	21
55°	4	5
65°	3	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P1294134  
CATALOG NUMBER: P3AS09R55W2N902750DE010 E3DL1GPH\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	393.2
2.5°	392.1
5°	387.7
7.5°	380.8
10°	370.2
12.5°	355.2
15°	335.6
17.5°	310.8
20°	281.7
22.5°	249.2
25°	214.6
27.5°	179.2
30°	145.5
32.5°	114.9
35°	88.7
37.5°	67.4
40°	49.8
42.5°	35.7
45°	25.9
47.5°	18.7
50°	12.7
52.5°	7.2
55°	4.0
57.5°	3.5
60°	3.2
62.5°	2.9
65°	2.6
67.5°	2.3
70°	2.0
72.5°	1.7
75°	1.4
77.5°	1.2
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)