

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296120

Luminaire Tested: P3AS13R25W2N902765DE010 E3CB1MW\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296120  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902765DE010 E3CB1MW\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,  
E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 987.1 lumens  
Efficiency: N/A  
Efficacy: 80.3 lumens/watt  
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296120  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3CB1MW\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296120  
 CATALOG NUMBER: P3AS13R25W2N902765DE010 E3CB1MW\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99		97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96		94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93		92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90		89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88		87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86		85
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83		83
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81		81
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80		79
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78		77

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1055244
5°	978712
10°	759015
15°	380592
20°	125031
25°	49721
30°	18661
35°	5407
40°	2433
45°	961
50°	785
55°	612
60°	702
65°	830
70°	513
75°	678
80°	1010
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 80°  
 Luminance: 1010 cd/sqm



TEST NUMBER: P1296120

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3CB1MW\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	391.1	39.6
10°-20°	466.6	47.3
20°-30°	105.2	10.7
30°-40°	17.1	1.7
40°-50°	3.1	0.3
50°-60°	1.7	0.2
60°-70°	1.5	0.2
70°-80°	0.8	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	962.9	97.5
0°-40°	979.9	99.3
0°-60°	984.7	99.8
0°-90°	987.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	987.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4812	
5°	4446	391
15°	1676	467
25°	206	105
35°	20	17
45°	3	3
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1296120  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3CB1MW\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4812.3
1°	4804.6
2°	4765.8
3°	4694.4
4°	4586.7
5°	4446.3
6°	4278.8
7°	4097.4
8°	3889.5
9°	3662.3
10°	3408.8
11°	3116.4
12°	2779.9
13°	2427.9
14°	2050.2
15°	1676.5
17.5°	955.3
20°	535.8
22.5°	323.4
25°	205.5
27.5°	126.4
30°	73.7
32.5°	38.8
35°	20.2
37.5°	13.2
40°	8.5
42.5°	5.4
45°	3.1
47.5°	2.3
50°	2.3
52.5°	2.3
55°	1.6
57.5°	1.6
60°	1.6
62.5°	1.6
65°	1.6
67.5°	1.6
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1296120  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3CB1MW\_4000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)