

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296166

Luminaire Tested: P3AS13R25W2N902765DE010 E3D1WMH\_3000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296166  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902765DE010 E3D1WMH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,  
E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1033.0 lumens  
Efficiency: N/A  
Efficacy: 84.0 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296166  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3D1WMH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296166  
 CATALOG NUMBER: P3AS13R25W2N902765DE010 E3D1WMH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 115 | 113 | 111 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 102 | 100 | 99  | 99  | 99  | 99  | 99  | 97  |
| 2   | 112 | 108 | 106 | 103 | 110 | 107 | 104 | 102 | 104 | 102 | 100 | 101 | 99  | 98  | 98  | 97  | 96  | 96  | 96  | 96  | 94  |
| 3   | 109 | 104 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 98  | 96  | 98  | 96  | 94  | 96  | 94  | 93  | 96  | 94  | 93  | 92  |
| 4   | 106 | 101 | 97  | 94  | 104 | 100 | 96  | 94  | 98  | 95  | 92  | 96  | 93  | 91  | 94  | 92  | 90  | 94  | 92  | 90  | 89  |
| 5   | 103 | 97  | 93  | 91  | 101 | 96  | 93  | 90  | 95  | 92  | 90  | 93  | 91  | 89  | 92  | 90  | 88  | 92  | 90  | 88  | 87  |
| 6   | 100 | 94  | 90  | 88  | 99  | 94  | 90  | 87  | 92  | 89  | 87  | 91  | 88  | 86  | 90  | 88  | 86  | 90  | 88  | 86  | 85  |
| 7   | 98  | 92  | 88  | 85  | 97  | 91  | 87  | 85  | 90  | 87  | 84  | 89  | 86  | 84  | 88  | 86  | 84  | 88  | 86  | 84  | 83  |
| 8   | 95  | 89  | 85  | 83  | 94  | 89  | 85  | 83  | 88  | 85  | 82  | 87  | 84  | 82  | 86  | 84  | 82  | 86  | 84  | 82  | 81  |
| 9   | 93  | 87  | 83  | 81  | 92  | 86  | 83  | 80  | 86  | 83  | 80  | 85  | 82  | 80  | 84  | 82  | 80  | 84  | 82  | 80  | 79  |
| 10  | 91  | 85  | 81  | 79  | 90  | 84  | 81  | 79  | 84  | 81  | 78  | 83  | 80  | 78  | 83  | 80  | 78  | 83  | 80  | 78  | 77  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1131335 |
| 5°  | 1048005 |
| 10° | 810851  |
| 15° | 387289  |
| 20° | 127691  |
| 25° | 53834   |
| 30° | 20864   |
| 35° | 9021    |
| 40° | 3006    |
| 45° | 1395    |
| 50° | 512     |
| 55° | 268     |
| 60° | 175     |
| 65° | 208     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1395 cd/sqm



TEST NUMBER: P1296166

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3D1WMH\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 418.5  | 40.5      |
| 10°-20°   | 476.0  | 46.1      |
| 20°-30°   | 110.6  | 10.7      |
| 30°-40°   | 23.2   | 2.2       |
| 40°-50°   | 3.7    | 0.4       |
| 50°-60°   | 0.6    | 0.1       |
| 60°-70°   | 0.3    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1005.1 | 97.3      |
| 0°-40°    | 1028.3 | 99.5      |
| 0°-60°    | 1032.6 | 100.0     |
| 0°-90°    | 1033.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1033.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5159 |      |
| 5°  | 4761 | 419  |
| 15° | 1706 | 476  |
| 25° | 222  | 111  |
| 35° | 34   | 23   |
| 45° | 4    | 4    |
| 55° | 1    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P1296166  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3D1WMH\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 5159.3 |
| 1°    | 5148.8 |
| 2°    | 5095.2 |
| 3°    | 5019.9 |
| 4°    | 4905.0 |
| 5°    | 4761.1 |
| 6°    | 4576.5 |
| 7°    | 4383.2 |
| 8°    | 4166.4 |
| 9°    | 3921.8 |
| 10°   | 3641.6 |
| 11°   | 3316.9 |
| 12°   | 2944.2 |
| 13°   | 2536.0 |
| 14°   | 2109.0 |
| 15°   | 1706.0 |
| 16°   | 1349.5 |
| 17°   | 1051.3 |
| 18°   | 827.0  |
| 19°   | 661.4  |
| 20°   | 547.2  |
| 21°   | 457.3  |
| 22°   | 383.9  |
| 23°   | 320.6  |
| 24°   | 268.2  |
| 25°   | 222.5  |
| 27.5° | 131.8  |
| 30°   | 82.4   |
| 32.5° | 52.8   |
| 35°   | 33.7   |
| 37.5° | 20.2   |
| 40°   | 10.5   |
| 42.5° | 6.7    |
| 45°   | 4.5    |
| 47.5° | 2.6    |
| 50°   | 1.5    |
| 52.5° | 0.7    |
| 55°   | 0.7    |
| 57.5° | 0.4    |
| 60°   | 0.4    |
| 62.5° | 0.4    |
| 65°   | 0.4    |
| 67.5° | 0.4    |
| 70°   | 0.0    |
| 72.5° | 0.0    |



TEST NUMBER: P1296166  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3D1WMH\_3000K

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)