

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296176

Luminaire Tested: P3AS13R25W2N902765DE010 E3DL1GPH\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296176  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902765DE010 E3DL1GPH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 6500K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 396.0 lumens  
Efficiency: N/A  
Efficacy: 32.2 lumens/watt  
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296176  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DL1GPH\_6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296176

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DL1GPH\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	254015
5°	237001
10°	189843
15°	128877
20°	77987
25°	45607
30°	25979
35°	14295
40°	7586
45°	4000
50°	2320
55°	1720
60°	1491
65°	1557
70°	1475
75°	1271
80°	1010
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4000 cd/sqm



TEST NUMBER: P1296176

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DL1GPH\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.5	24.1
10°-20°	156.1	39.4
20°-30°	89.2	22.5
30°-40°	35.2	8.9
40°-50°	10.8	2.7
50°-60°	4.3	1.1
60°-70°	2.8	0.7
70°-80°	1.6	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	340.8	86.1
0°-40°	376.0	94.9
0°-60°	391.1	98.7
0°-90°	396.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	396.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1158	
5°	1077	96
15°	568	156
25°	188	89
35°	53	35
45°	13	11
55°	4	4
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1296176  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DL1GPH\_6500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1158.4
1°	1156.1
2°	1146.7
3°	1130.0
4°	1107.0
5°	1076.7
6°	1041.1
7°	1001.0
8°	954.4
9°	906.8
10°	852.6
11°	799.3
12°	740.6
13°	682.7
14°	623.3
15°	567.7
17.5°	440.1
20°	334.2
22.5°	250.9
25°	188.5
27.5°	139.6
30°	102.6
32.5°	74.2
35°	53.4
37.5°	37.8
40°	26.5
42.5°	18.2
45°	12.9
47.5°	9.1
50°	6.8
52.5°	5.3
55°	4.5
57.5°	4.2
60°	3.4
62.5°	3.0
65°	3.0
67.5°	2.6
70°	2.3
72.5°	1.9
75°	1.5
77.5°	1.1
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4



TEST NUMBER: P1296176  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DL1GPH\_6500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)