

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296293

Luminaire Tested: P3AS13R25W2N902765DE010 E3PHLP1MW\_3500K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296293  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902765DE010 E3PHLP1MW\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3500K CCT AND, 90CRI ,  
E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 447.0 lumens  
Efficiency: N/A  
Efficacy: 36.3 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296293  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3PHLP1MW\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296293

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3PHLP1MW\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	150185
5°	141888
10°	120617
15°	95528
20°	72596
25°	54148
30°	39398
35°	27867
40°	18893
45°	13180
50°	11087
55°	10705
60°	11271
65°	11623
70°	11476
75°	12285
80°	14143
85°	14089

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 15120 cd/sqm



TEST NUMBER: P1296293

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3PHLP1MW\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.2	13.0
10°-20°	116.5	26.1
20°-30°	103.1	23.1
30°-40°	65.7	14.7
40°-50°	34.7	7.8
50°-60°	25.6	5.7
60°-70°	21.7	4.9
70°-80°	15.3	3.4
80°-90°	6.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	277.8	62.1
0°-40°	343.5	76.8
0°-60°	403.8	90.3
0°-90°	447.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	447.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	685	
5°	645	58
15°	421	116
25°	224	103
35°	104	66
45°	42	35
55°	28	26
65°	22	22
75°	14	15
85°	6	6
90°	0	



TEST NUMBER: P1296293

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3PHLP1MW\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	684.9
2.5°	674.9
5°	644.6
7.5°	597.6
10°	541.7
12.5°	481.2
15°	420.8
17.5°	362.6
20°	311.1
22.5°	264.1
25°	223.8
27.5°	188.0
30°	155.6
32.5°	127.6
35°	104.1
37.5°	82.8
40°	66.0
42.5°	52.6
45°	42.5
47.5°	36.9
50°	32.5
52.5°	30.2
55°	28.0
57.5°	26.9
60°	25.7
62.5°	23.5
65°	22.4
67.5°	20.1
70°	17.9
72.5°	16.8
75°	14.5
77.5°	12.3
80°	11.2
82.5°	9.0
85°	5.6
87.5°	2.2
90°	0.0

(END OF REPORT)