

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296295

Luminaire Tested: P3AS13R25W2N902765DE010 E3PHLP1MW\_5000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296295  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902765DE010 E3PHLP1MW\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,  
E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 445.0 lumens  
Efficiency: N/A  
Efficacy: 36.2 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296295  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3PHLP1MW\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296295

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3PHLP1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	149527
5°	141272
10°	120082
15°	95097
20°	72270
25°	53906
30°	39221
35°	27733
40°	18807
45°	13118
50°	11019
55°	10666
60°	11227
65°	11571
70°	11412
75°	12285
80°	14017
85°	14089

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 14952 cd/sqm



TEST NUMBER: P1296295

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3PHLP1MW\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.9	13.0
10°-20°	116.0	26.1
20°-30°	102.7	23.1
30°-40°	65.4	14.7
40°-50°	34.6	7.8
50°-60°	25.4	5.7
60°-70°	21.7	4.9
70°-80°	15.3	3.4
80°-90°	6.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	276.5	62.1
0°-40°	341.9	76.8
0°-60°	402.0	90.3
0°-90°	445.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	445.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	682	
5°	642	58
15°	419	116
25°	223	103
35°	104	65
45°	42	35
55°	28	25
65°	22	22
75°	14	15
85°	6	6
90°	0	



TEST NUMBER: P1296295  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3PHLP1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	681.9
2.5°	671.8
5°	641.8
7.5°	595.0
10°	539.3
12.5°	479.1
15°	418.9
17.5°	361.0
20°	309.7
22.5°	262.9
25°	222.8
27.5°	187.2
30°	154.9
32.5°	127.0
35°	103.6
37.5°	82.4
40°	65.7
42.5°	52.4
45°	42.3
47.5°	36.8
50°	32.3
52.5°	30.1
55°	27.9
57.5°	26.7
60°	25.6
62.5°	23.4
65°	22.3
67.5°	20.1
70°	17.8
72.5°	16.7
75°	14.5
77.5°	12.3
80°	11.1
82.5°	8.9
85°	5.6
87.5°	2.2
90°	0.0

(END OF REPORT)