

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296311

Luminaire Tested: P3AS13R30W2N902750DE010 E3CB1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296311
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30W2N902750DE010 E3CB1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 90CRI ,
E3CB1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 982.0 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296311
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3CB1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296311

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3CB1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 99 | 98 | 100 |
| 1 | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 98 | 96 | 95 | 97 |
| 2 | 111 | 108 | 105 | 102 | 109 | 106 | 104 | 101 | 103 | 101 | 99 | 100 | 99 | 97 | 98 | 96 | 95 | 95 | 94 | 92 | 94 |
| 3 | 108 | 103 | 100 | 97 | 106 | 102 | 99 | 96 | 100 | 97 | 95 | 97 | 95 | 93 | 95 | 94 | 92 | 93 | 91 | 89 | 91 |
| 4 | 105 | 100 | 96 | 93 | 103 | 99 | 95 | 92 | 97 | 94 | 91 | 95 | 92 | 90 | 93 | 91 | 89 | 93 | 91 | 89 | 88 |
| 5 | 102 | 96 | 92 | 89 | 100 | 95 | 91 | 89 | 94 | 90 | 88 | 92 | 89 | 87 | 91 | 88 | 87 | 91 | 88 | 87 | 85 |
| 6 | 99 | 93 | 89 | 86 | 98 | 92 | 88 | 86 | 91 | 88 | 85 | 90 | 87 | 85 | 89 | 86 | 84 | 89 | 86 | 84 | 83 |
| 7 | 96 | 90 | 86 | 83 | 95 | 89 | 86 | 83 | 88 | 85 | 82 | 87 | 84 | 82 | 86 | 84 | 82 | 86 | 84 | 82 | 81 |
| 8 | 94 | 87 | 83 | 81 | 93 | 87 | 83 | 80 | 86 | 83 | 80 | 85 | 82 | 80 | 84 | 82 | 80 | 84 | 82 | 80 | 79 |
| 9 | 91 | 85 | 81 | 78 | 90 | 84 | 81 | 78 | 84 | 80 | 78 | 83 | 80 | 78 | 82 | 79 | 77 | 82 | 79 | 77 | 77 |
| 10 | 89 | 83 | 79 | 76 | 88 | 82 | 78 | 76 | 82 | 78 | 76 | 81 | 78 | 76 | 80 | 77 | 75 | 80 | 77 | 75 | 75 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 799673 |
| 5° | 784568 |
| 10° | 694532 |
| 15° | 440025 |
| 20° | 167035 |
| 25° | 49454 |
| 30° | 19522 |
| 35° | 5996 |
| 40° | 2662 |
| 45° | 961 |
| 50° | 785 |
| 55° | 573 |
| 60° | 658 |
| 65° | 778 |
| 70° | 513 |
| 75° | 678 |
| 80° | 1010 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 80°
 Luminance: 1010 cd/sqm



TEST NUMBER: P1296311

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3CB1MW_5000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 327.7 | 33.4 |
| 10°-20° | 510.6 | 52.0 |
| 20°-30° | 118.6 | 12.1 |
| 30°-40° | 18.4 | 1.9 |
| 40°-50° | 3.1 | 0.3 |
| 50°-60° | 1.4 | 0.1 |
| 60°-70° | 1.2 | 0.1 |
| 70°-80° | 0.8 | 0.1 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 956.9 | 97.4 |
| 0°-40° | 975.3 | 99.3 |
| 0°-60° | 979.8 | 99.8 |
| 0°-90° | 982.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 982.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3647 | |
| 5° | 3564 | 328 |
| 15° | 1938 | 511 |
| 25° | 204 | 119 |
| 35° | 22 | 18 |
| 45° | 3 | 3 |
| 55° | 2 | 1 |
| 65° | 2 | 1 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1296311
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3CB1MW_5000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 3646.8 |
| 1° | 3644.5 |
| 2° | 3634.5 |
| 3° | 3617.5 |
| 4° | 3595.9 |
| 5° | 3564.3 |
| 6° | 3525.0 |
| 7° | 3466.3 |
| 8° | 3386.1 |
| 9° | 3268.1 |
| 10° | 3119.2 |
| 11° | 2927.2 |
| 12° | 2710.4 |
| 13° | 2469.8 |
| 14° | 2205.2 |
| 15° | 1938.3 |
| 17.5° | 1268.1 |
| 20° | 715.8 |
| 22.5° | 365.6 |
| 25° | 204.4 |
| 27.5° | 125.7 |
| 30° | 77.1 |
| 32.5° | 41.7 |
| 35° | 22.4 |
| 37.5° | 14.7 |
| 40° | 9.3 |
| 42.5° | 5.4 |
| 45° | 3.1 |
| 47.5° | 2.3 |
| 50° | 2.3 |
| 52.5° | 1.5 |
| 55° | 1.5 |
| 57.5° | 1.5 |
| 60° | 1.5 |
| 62.5° | 1.5 |
| 65° | 1.5 |
| 67.5° | 0.8 |
| 70° | 0.8 |
| 72.5° | 0.8 |
| 75° | 0.8 |
| 77.5° | 0.8 |
| 80° | 0.8 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |



TEST NUMBER: P1296311
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3CB1MW_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)