

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296313

Luminaire Tested: P3AS13R30W2N902750DE010 E3CD1MB_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30W2N902750DE010 E3CD1MB_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 973.0 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296313
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3CD1MB_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296313

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3CD1MB_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 324.7 | 33.4 |
| 10°-20° | 505.9 | 52.0 |
| 20°-30° | 117.5 | 12.1 |
| 30°-40° | 18.2 | 1.9 |
| 40°-50° | 3.1 | 0.3 |
| 50°-60° | 1.4 | 0.1 |
| 60°-70° | 1.2 | 0.1 |
| 70°-80° | 0.8 | 0.1 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 948.1 | 97.4 |
| 0°-40° | 966.3 | 99.3 |
| 0°-60° | 970.9 | 99.8 |
| 0°-90° | 973.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 973.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3613 | |
| 5° | 3532 | 325 |
| 15° | 1921 | 506 |
| 25° | 202 | 117 |
| 35° | 22 | 18 |
| 45° | 3 | 3 |
| 55° | 2 | 1 |
| 65° | 2 | 1 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1296313
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3CD1MB_3000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 3613.4 |
| 1° | 3611.1 |
| 2° | 3601.2 |
| 3° | 3584.4 |
| 4° | 3563.0 |
| 5° | 3531.6 |
| 6° | 3492.7 |
| 7° | 3434.6 |
| 8° | 3355.1 |
| 9° | 3238.2 |
| 10° | 3090.7 |
| 11° | 2900.4 |
| 12° | 2685.6 |
| 13° | 2447.1 |
| 14° | 2185.0 |
| 15° | 1920.6 |
| 17.5° | 1256.4 |
| 20° | 709.2 |
| 22.5° | 362.3 |
| 25° | 202.5 |
| 27.5° | 124.6 |
| 30° | 76.4 |
| 32.5° | 41.3 |
| 35° | 22.2 |
| 37.5° | 14.5 |
| 40° | 9.2 |
| 42.5° | 5.3 |
| 45° | 3.1 |
| 47.5° | 2.3 |
| 50° | 2.3 |
| 52.5° | 1.5 |
| 55° | 1.5 |
| 57.5° | 1.5 |
| 60° | 1.5 |
| 62.5° | 1.5 |
| 65° | 1.5 |
| 67.5° | 0.8 |
| 70° | 0.8 |
| 72.5° | 0.8 |
| 75° | 0.8 |
| 77.5° | 0.8 |
| 80° | 0.8 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |



TEST NUMBER: P1296313

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3CD1MB_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)