

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296352

Luminaire Tested: P3AS13R30W2N902750DE010 E3DL1GPH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296352  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R30W2N902750DE010 E3DL1GPH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 360.0 lumens  
Efficiency: N/A  
Efficacy: 29.3 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296352  
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DL1GPH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296352  
 CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DL1GPH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	91	89	87	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	88	85	83	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	81	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71	78	75	73	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	76	72	70	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	71	67	65	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	210071
5°	199933
10°	168178
15°	121295
20°	75233
25°	42777
30°	23776
35°	12930
40°	6813
45°	3690
50°	1979
55°	1300
60°	1184
65°	1245
70°	1090
75°	847
80°	884
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3690 cd/sqm



TEST NUMBER: P1296352

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DL1GPH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.8	22.7
10°-20°	145.4	40.4
20°-30°	84.0	23.3
30°-40°	31.9	8.9
40°-50°	9.8	2.7
50°-60°	3.3	0.9
60°-70°	2.2	0.6
70°-80°	1.2	0.3
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	311.2	86.4
0°-40°	343.1	95.3
0°-60°	356.2	98.9
0°-90°	360.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	360.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	958	
5°	908	82
15°	534	145
25°	177	84
35°	48	32
45°	12	10
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1296352  
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DL1GPH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	958.0
1°	957.3
2°	951.5
3°	940.7
4°	927.1
5°	908.3
6°	884.5
7°	858.0
8°	828.4
9°	793.1
10°	755.3
11°	714.5
12°	671.3
13°	626.1
14°	580.2
15°	534.3
17.5°	421.4
20°	322.4
22.5°	239.1
25°	176.8
27.5°	128.5
30°	93.9
32.5°	67.7
35°	48.3
37.5°	33.7
40°	23.8
42.5°	16.7
45°	11.9
47.5°	8.2
50°	5.8
52.5°	4.1
55°	3.4
57.5°	3.1
60°	2.7
62.5°	2.4
65°	2.4
67.5°	2.0
70°	1.7
72.5°	1.4
75°	1.0
77.5°	1.0
80°	0.7
82.5°	0.7
85°	0.3
87.5°	0.0



TEST NUMBER: P1296352  
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DL1GPH\_2700K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)