

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294502

Luminaire Tested: P3AS09R60W2N902750DE010 E3DLD1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R60W2N902750DE010 E3DLD1WH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 4000K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 488.0 lumens
Efficiency: N/A
Efficacy: 54.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294502
CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLD1WH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294502
 CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLD1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86638
5°	85648
10°	82697
15°	78116
20°	72013
25°	65205
30°	57882
35°	49470
40°	39331
45°	27724
50°	16579
55°	8372
60°	8070
65°	7368
70°	6860
75°	6524
80°	5935
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27724 cd/sqm



TEST NUMBER: P1294502
 CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLD1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.6	7.5
10°-20°	96.2	19.7
20°-30°	123.5	25.3
30°-40°	114.5	23.5
40°-50°	69.7	14.3
50°-60°	23.2	4.8
60°-70°	14.1	2.9
70°-80°	8.0	1.6
80°-90°	2.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	256.2	52.5
0°-40°	370.7	76.0
0°-60°	463.6	95.0
0°-90°	488.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	488.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	395	
5°	389	37
15°	344	96
25°	270	123
35°	185	114
45°	89	70
55°	22	23
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1294502
CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLD1WH_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	395.1
2.5°	393.3
5°	389.1
7.5°	381.4
10°	371.4
12.5°	358.9
15°	344.1
17.5°	326.9
20°	308.6
22.5°	289.0
25°	269.5
27.5°	249.4
30°	228.6
32.5°	207.9
35°	184.8
37.5°	160.5
40°	137.4
42.5°	113.1
45°	89.4
47.5°	69.3
50°	48.6
52.5°	29.0
55°	21.9
57.5°	20.1
60°	18.4
62.5°	16.0
65°	14.2
67.5°	12.4
70°	10.7
72.5°	8.9
75°	7.7
77.5°	5.9
80°	4.7
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)