

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294514

Luminaire Tested: P3AS09R60W2N902750DE010 E3DLP1H\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294514  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R60W2N902750DE010 E3DLP1H\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,  
E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 384.0 lumens  
Efficiency: N/A  
Efficacy: 42.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294514  
CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLP1H\_2700K

### Luminous Intensity Polar Plot







TEST NUMBER: P1294514  
 CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLP1H\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.2	10.5
10°-20°	97.8	25.5
20°-30°	107.2	27.9
30°-40°	78.1	20.3
40°-50°	36.9	9.6
50°-60°	12.1	3.1
60°-70°	6.8	1.8
70°-80°	3.7	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	245.2	63.9
0°-40°	323.3	84.2
0°-60°	372.3	97.0
0°-90°	384.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	384.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	444	
5°	432	40
15°	352	98
25°	235	107
35°	124	78
45°	46	37
55°	12	12
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1294514  
CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLP1H\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	443.8
2.5°	441.2
5°	432.2
7.5°	418.5
10°	400.0
12.5°	377.8
15°	352.0
17.5°	324.0
20°	294.5
22.5°	264.4
25°	234.8
27.5°	205.3
30°	177.3
32.5°	150.4
35°	124.5
37.5°	101.3
40°	80.2
42.5°	61.7
45°	46.4
47.5°	33.8
50°	23.2
52.5°	15.3
55°	12.1
57.5°	10.6
60°	9.5
62.5°	7.9
65°	6.9
67.5°	5.8
70°	4.7
72.5°	4.2
75°	3.7
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)