

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296444

Luminaire Tested: P3AS13R30W2N902750DE010 E3PH1MW_3500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296444
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30W2N902750DE010 E3PH1MW_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3500K CCT AND, 90CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 799.0 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296444
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PH1MW_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1296444
 CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PH1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99		97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96		95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94		93
4	106	101	98	95	105	100	97	95	98	96	94	97	94	92	95	93	91		90
5	104	98	95	92	102	97	94	91	96	93	91	94	92	90	93	91	89		88
6	101	95	92	89	100	95	91	89	94	91	88	92	90	88	91	89	87		86
7	99	93	89	87	98	92	89	86	91	88	86	90	88	86	89	87	85		84
8	96	91	87	84	96	90	87	84	89	86	84	88	86	84	88	85	83		83
9	94	89	85	82	94	88	85	82	87	84	82	87	84	82	86	84	82		81
10	92	87	83	81	92	86	83	81	86	82	80	85	82	80	84	82	80		79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1137277
5°	993416
10°	544991
15°	250739
20°	135135
25°	45801
30°	5950
35°	910
40°	315
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1296444

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PH1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	361.6	45.3
10°-20°	331.4	41.5
20°-30°	101.9	12.8
30°-40°	3.8	0.5
40°-50°	0.3	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	794.9	99.5
0°-40°	798.7	100.0
0°-60°	799.0	100.0
0°-90°	799.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	799.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5186	
5°	4513	362
15°	1104	331
25°	189	102
35°	3	4
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1296444
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PH1MW_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	5186.4
2.5°	5065.4
5°	4513.1
7.5°	3540.8
10°	2447.6
12.5°	1656.7
15°	1104.5
17.5°	774.0
20°	579.1
22.5°	389.8
25°	189.3
27.5°	69.5
30°	23.5
32.5°	7.8
35°	3.4
37.5°	2.2
40°	1.1
42.5°	1.1
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)