

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296448

Luminaire Tested: P3AS13R30W2N902750DE010 E3PHLD1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296448
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30W2N902750DE010 E3PHLD1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 595.0 lumens
Efficiency: N/A
Efficacy: 48.4 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296448
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PHLD1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296448

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PHLD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	71
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	48	46
9	68	57	50	45	66	56	49	45	55	49	45	54	49	45	53	48	44	43
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146611
5°	140127
10°	120862
15°	100182
20°	82140
25°	66197
30°	53350
35°	43714
40°	36325
45°	30794
50°	26336
55°	22785
60°	20305
65°	17745
70°	15580
75°	13047
80°	9723
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30794 cd/sqm



TEST NUMBER: P1296448

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PHLD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.7	9.7
10°-20°	123.1	20.7
20°-30°	126.1	21.2
30°-40°	103.1	17.3
40°-50°	77.1	13.0
50°-60°	54.2	9.1
60°-70°	34.1	5.7
70°-80°	16.4	2.8
80°-90°	3.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.9	51.6
0°-40°	410.0	68.9
0°-60°	541.3	91.0
0°-90°	595.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	595.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	669	
5°	637	58
15°	441	123
25°	274	126
35°	163	103
45°	99	77
55°	60	54
65°	34	34
75°	15	16
85°	2	3
90°	0	



TEST NUMBER: P1296448
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PHLD1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	668.6
2.5°	662.0
5°	636.6
7.5°	594.7
10°	542.8
12.5°	492.1
15°	441.3
17.5°	395.0
20°	352.0
22.5°	311.1
25°	273.6
27.5°	240.5
30°	210.7
32.5°	186.5
35°	163.3
37.5°	144.5
40°	126.9
42.5°	112.5
45°	99.3
47.5°	87.2
50°	77.2
52.5°	68.4
55°	59.6
57.5°	53.0
60°	46.3
62.5°	39.7
65°	34.2
67.5°	28.7
70°	24.3
72.5°	19.9
75°	15.4
77.5°	11.0
80°	7.7
82.5°	4.4
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)