

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296453

Luminaire Tested: P3AS13R30W2N902750DE010 E3PHLP1MW\_3000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296453  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R30W2N902750DE010 E3PHLP1MW\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,  
E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 430.0 lumens  
Efficiency: N/A  
Efficacy: 35.0 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.67  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296453  
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PHLP1MW\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296453

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PHLP1MW\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68	68	68	68
5	88	78	72	67	86	77	71	66	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	67	62	82	72	66	62	71	65	61	69	64	61	68	64	60	59	59	59	59
7	79	69	62	57	78	68	62	57	67	61	57	66	60	57	64	60	56	55	55	55	55
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	51	51
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	139616
5°	131653
10°	112534
15°	90171
20°	70286
25°	52866
30°	38563
35°	27171
40°	18635
45°	13335
50°	10916
55°	10552
60°	10657
65°	10896
70°	11348
75°	12115
80°	12502
85°	13838

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 14784 cd/sqm



TEST NUMBER: P1296453

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PHLP1MW\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.1	12.6
10°-20°	110.4	25.7
20°-30°	100.6	23.4
30°-40°	64.0	14.9
40°-50°	34.3	8.0
50°-60°	25.1	5.8
60°-70°	21.1	4.9
70°-80°	14.7	3.4
80°-90°	5.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	265.1	61.6
0°-40°	329.1	76.5
0°-60°	388.4	90.3
0°-90°	430.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	430.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	637	
5°	598	54
15°	397	110
25°	218	101
35°	102	64
45°	43	34
55°	28	25
65°	21	21
75°	14	15
85°	6	6
90°	0	



TEST NUMBER: P1296453  
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PHLP1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	636.7
2.5°	626.8
5°	598.1
7.5°	556.1
10°	505.4
12.5°	451.3
15°	397.2
17.5°	347.6
20°	301.2
22.5°	258.2
25°	218.5
27.5°	183.2
30°	152.3
32.5°	123.6
35°	101.5
37.5°	80.6
40°	65.1
42.5°	51.9
45°	43.0
47.5°	35.3
50°	32.0
52.5°	29.8
55°	27.6
57.5°	26.5
60°	24.3
62.5°	23.2
65°	21.0
67.5°	19.9
70°	17.7
72.5°	15.4
75°	14.3
77.5°	12.1
80°	9.9
82.5°	8.8
85°	5.5
87.5°	2.2
90°	0.0

(END OF REPORT)