

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294612

Luminaire Tested: P3AS09R60W2N902765DE010 E3DL1H\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294612  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R60W2N902765DE010 E3DL1H\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,  
E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 613.0 lumens  
Efficiency: N/A  
Efficacy: 68.1 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294612  
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DL1H\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1294612  
 CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DL1H\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 96  | 94  | 93  | 93  | 93  | 93  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  | 94  | 91  | 89  | 91  | 89  | 87  | 85  | 85  | 85  | 85  |
| 3   | 101 | 95  | 89  | 85  | 99  | 93  | 88  | 84  | 91  | 86  | 83  | 88  | 85  | 82  | 86  | 83  | 80  | 79  | 79  | 79  | 79  |
| 4   | 96  | 88  | 82  | 78  | 94  | 87  | 81  | 77  | 85  | 80  | 76  | 83  | 79  | 75  | 81  | 77  | 75  | 73  | 73  | 73  | 73  |
| 5   | 91  | 82  | 76  | 71  | 89  | 81  | 75  | 71  | 79  | 74  | 70  | 78  | 73  | 70  | 76  | 72  | 69  | 68  | 68  | 68  | 68  |
| 6   | 86  | 77  | 70  | 66  | 84  | 76  | 70  | 66  | 74  | 69  | 65  | 73  | 68  | 65  | 72  | 68  | 64  | 63  | 63  | 63  | 63  |
| 7   | 82  | 72  | 66  | 61  | 80  | 71  | 65  | 61  | 70  | 65  | 61  | 69  | 64  | 60  | 68  | 63  | 60  | 59  | 59  | 59  | 59  |
| 8   | 77  | 68  | 61  | 57  | 76  | 67  | 61  | 57  | 66  | 60  | 57  | 65  | 60  | 56  | 64  | 59  | 56  | 55  | 55  | 55  | 55  |
| 9   | 74  | 64  | 57  | 53  | 72  | 63  | 57  | 53  | 62  | 57  | 53  | 61  | 56  | 53  | 60  | 56  | 53  | 51  | 51  | 51  | 51  |
| 10  | 70  | 60  | 54  | 50  | 69  | 60  | 54  | 50  | 59  | 53  | 50  | 58  | 53  | 50  | 57  | 53  | 49  | 48  | 48  | 48  | 48  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 144747 |
| 5°  | 143385 |
| 10° | 139209 |
| 15° | 130421 |
| 20° | 115417 |
| 25° | 96562  |
| 30° | 75683  |
| 35° | 54904  |
| 40° | 36526  |
| 45° | 22762  |
| 50° | 12315  |
| 55° | 3555   |
| 60° | 3333   |
| 65° | 3009   |
| 70° | 3013   |
| 75° | 2965   |
| 80° | 2904   |
| 85° | 3019   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22762 cd/sqm



TEST NUMBER: P1294612  
 CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DL1H\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 61.3   | 10.0      |
| 10°-20°   | 159.4  | 26.0      |
| 20°-30°   | 181.7  | 29.6      |
| 30°-40°   | 128.8  | 21.0      |
| 40°-50°   | 58.5   | 9.5       |
| 50°-60°   | 12.4   | 2.0       |
| 60°-70°   | 6.0    | 1.0       |
| 70°-80°   | 3.7    | 0.6       |
| 80°-90°   | 1.3    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 402.4  | 65.6      |
| 0°-40°    | 531.2  | 86.7      |
| 0°-60°    | 602.1  | 98.2      |
| 0°-90°    | 613.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 613.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 660 |      |
| 5°  | 651 | 61   |
| 15° | 574 | 159  |
| 25° | 399 | 182  |
| 35° | 205 | 129  |
| 45° | 73  | 58   |
| 55° | 9   | 12   |
| 65° | 6   | 6    |
| 75° | 4   | 4    |
| 85° | 1   | 1    |
| 90° | 0   |      |



TEST NUMBER: P1294612  
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DL1H\_3000K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 660.1 |
| 2.5°  | 657.8 |
| 5°    | 651.4 |
| 7.5°  | 640.3 |
| 10°   | 625.2 |
| 12.5° | 603.6 |
| 15°   | 574.5 |
| 17.5° | 537.8 |
| 20°   | 494.6 |
| 22.5° | 448.0 |
| 25°   | 399.1 |
| 27.5° | 349.0 |
| 30°   | 298.9 |
| 32.5° | 251.1 |
| 35°   | 205.1 |
| 37.5° | 164.3 |
| 40°   | 127.6 |
| 42.5° | 96.7  |
| 45°   | 73.4  |
| 47.5° | 54.8  |
| 50°   | 36.1  |
| 52.5° | 16.9  |
| 55°   | 9.3   |
| 57.5° | 8.2   |
| 60°   | 7.6   |
| 62.5° | 7.0   |
| 65°   | 5.8   |
| 67.5° | 5.2   |
| 70°   | 4.7   |
| 72.5° | 4.1   |
| 75°   | 3.5   |
| 77.5° | 2.9   |
| 80°   | 2.3   |
| 82.5° | 1.7   |
| 85°   | 1.2   |
| 87.5° | 0.6   |
| 90°   | 0.0   |

(END OF REPORT)