

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296555

Luminaire Tested: P3AS13R30W2N902765DE010 E3DL1WMH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296555  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R30W2N902765DE010 E3DL1WMH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3500K CCT AND, 90CRI ,  
E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 821.0 lumens  
Efficiency: N/A  
Efficacy: 66.7 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296555  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DL1WMH\_3500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1296555

CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DL1WMH\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	186.5	22.7
10°-20°	331.6	40.4
20°-30°	191.6	23.3
30°-40°	72.7	8.9
40°-50°	22.3	2.7
50°-60°	7.5	0.9
60°-70°	5.1	0.6
70°-80°	2.8	0.3
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	709.7	86.4
0°-40°	782.5	95.3
0°-60°	812.3	98.9
0°-90°	821.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	821.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2185	
5°	2072	187
15°	1218	332
25°	403	192
35°	110	73
45°	27	22
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1296555  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DL1WMH\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2184.8
1°	2183.2
2°	2170.0
3°	2145.2
4°	2114.2
5°	2071.5
6°	2017.3
7°	1956.8
8°	1889.3
9°	1808.6
10°	1722.5
11°	1629.5
12°	1531.0
13°	1427.8
14°	1323.1
15°	1218.4
17.5°	960.9
20°	735.2
22.5°	545.2
25°	403.3
27.5°	293.2
30°	214.1
32.5°	154.3
35°	110.1
37.5°	76.8
40°	54.3
42.5°	38.0
45°	27.1
47.5°	18.6
50°	13.2
52.5°	9.3
55°	7.8
57.5°	7.0
60°	6.2
62.5°	5.4
65°	5.4
67.5°	4.7
70°	3.9
72.5°	3.1
75°	2.3
77.5°	2.3
80°	1.6
82.5°	1.6
85°	0.8
87.5°	0.0



TEST NUMBER: P1296555  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DL1WMH\_3500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)