

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294631

Luminaire Tested: P3AS09R60W2N902765DE010 E3DL1WH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294631  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R60W2N902765DE010 E3DL1WH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3500K CCT AND, 90CRI ,  
E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 430.0 lumens  
Efficiency: N/A  
Efficacy: 47.8 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294631  
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DL1WH\_3500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1294631

CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DL1WH\_3500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 45.1   | 10.5      |
| 10°-20°   | 109.5  | 25.5      |
| 20°-30°   | 120.1  | 27.9      |
| 30°-40°   | 87.5   | 20.3      |
| 40°-50°   | 41.3   | 9.6       |
| 50°-60°   | 13.5   | 3.1       |
| 60°-70°   | 7.7    | 1.8       |
| 70°-80°   | 4.1    | 1.0       |
| 80°-90°   | 1.3    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 274.6  | 63.9      |
| 0°-40°    | 362.1  | 84.2      |
| 0°-60°    | 416.9  | 97.0      |
| 0°-90°    | 430.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 430.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 497 |      |
| 5°  | 484 | 45   |
| 15° | 394 | 109  |
| 25° | 263 | 120  |
| 35° | 140 | 87   |
| 45° | 52  | 41   |
| 55° | 14  | 14   |
| 65° | 8   | 8    |
| 75° | 4   | 4    |
| 85° | 1   | 1    |
| 90° | 0   |      |



TEST NUMBER: P1294631

CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DL1WH\_3500K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 497.0 |
| 2.5°  | 494.0 |
| 5°    | 484.0 |
| 7.5°  | 468.6 |
| 10°   | 447.9 |
| 12.5° | 423.1 |
| 15°   | 394.1 |
| 17.5° | 362.8 |
| 20°   | 329.7 |
| 22.5° | 296.1 |
| 25°   | 263.0 |
| 27.5° | 229.9 |
| 30°   | 198.6 |
| 32.5° | 168.4 |
| 35°   | 139.5 |
| 37.5° | 113.5 |
| 40°   | 89.8  |
| 42.5° | 69.1  |
| 45°   | 52.0  |
| 47.5° | 37.8  |
| 50°   | 26.0  |
| 52.5° | 17.1  |
| 55°   | 13.6  |
| 57.5° | 11.8  |
| 60°   | 10.6  |
| 62.5° | 8.9   |
| 65°   | 7.7   |
| 67.5° | 6.5   |
| 70°   | 5.3   |
| 72.5° | 4.7   |
| 75°   | 4.1   |
| 77.5° | 3.0   |
| 80°   | 2.4   |
| 82.5° | 1.8   |
| 85°   | 1.2   |
| 87.5° | 0.6   |
| 90°   | 0.0   |

(END OF REPORT)