

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296560

Luminaire Tested: P3AS13R30W2N902765DE010 E3DLD1GPH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296560  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R30W2N902765DE010 E3DLD1GPH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 305.0 lumens  
Efficiency: N/A  
Efficacy: 24.8 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296560  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLD1GPH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296560  
 CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLD1GPH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91	91	91	91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83	83	83	83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76	76	76	76
4	94	85	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59	59	59	59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48	48	48	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45	45	45	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	72056
5°	70438
10°	65508
15°	58275
20°	50124
25°	42462
30°	35246
35°	27653
40°	19809
45°	12994
50°	7403
55°	4855
60°	4605
65°	4255
70°	3847
75°	3474
80°	3283
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12994 cd/sqm



TEST NUMBER: P1296560

CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLD1GPH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	29.7	9.7
10°-20°	71.4	23.4
20°-30°	80.4	26.4
30°-40°	64.2	21.1
40°-50°	33.0	10.8
50°-60°	12.4	4.1
60°-70°	8.1	2.7
70°-80°	4.4	1.4
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	181.5	59.5
0°-40°	245.7	80.6
0°-60°	291.2	95.5
0°-90°	305.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	305.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	329	
5°	320	30
15°	257	71
25°	176	80
35°	103	64
45°	42	33
55°	13	12
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1296560  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLD1GPH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	328.6
1°	328.6
2°	327.5
3°	325.6
4°	323.0
5°	320.0
6°	316.3
7°	311.4
8°	306.1
9°	300.2
10°	294.2
11°	287.4
12°	280.3
13°	272.8
14°	265.0
15°	256.7
17.5°	235.8
20°	214.8
22.5°	194.6
25°	175.5
27.5°	156.8
30°	139.2
32.5°	121.3
35°	103.3
37.5°	85.7
40°	69.2
42.5°	54.6
45°	41.9
47.5°	31.1
50°	21.7
52.5°	15.3
55°	12.7
57.5°	11.6
60°	10.5
62.5°	9.4
65°	8.2
67.5°	7.1
70°	6.0
72.5°	4.9
75°	4.1
77.5°	3.4
80°	2.6
82.5°	1.9
85°	1.1
87.5°	0.4



TEST NUMBER: P1296560  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLD1GPH\_3000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)