

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296579

Luminaire Tested: P3AS13R30W2N902765DE010 E3DLD1MW\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296579  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R30W2N902765DE010 E3DLD1MW\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3500K CCT AND, 90CRI ,  
E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 632.0 lumens  
Efficiency: N/A  
Efficacy: 51.4 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296579  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLD1MW\_3500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1296579

CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLD1MW\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.6	9.7
10°-20°	147.9	23.4
20°-30°	166.7	26.4
30°-40°	133.1	21.1
40°-50°	68.4	10.8
50°-60°	25.7	4.1
60°-70°	16.9	2.7
70°-80°	9.1	1.4
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	376.1	59.5
0°-40°	509.2	80.6
0°-60°	603.4	95.5
0°-90°	632.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	632.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	681	
5°	663	62
15°	532	148
25°	364	167
35°	214	133
45°	87	68
55°	26	26
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1296579  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLD1MW\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	680.9
1°	680.9
2°	678.6
3°	674.7
4°	669.3
5°	663.1
6°	655.3
7°	645.2
8°	634.4
9°	622.0
10°	609.6
11°	595.6
12°	580.9
13°	565.4
14°	549.1
15°	532.0
17.5°	488.6
20°	445.2
22.5°	403.3
25°	363.7
27.5°	324.9
30°	288.5
32.5°	251.3
35°	214.0
37.5°	177.6
40°	143.5
42.5°	113.2
45°	86.9
47.5°	64.4
50°	45.0
52.5°	31.8
55°	26.4
57.5°	24.0
60°	21.7
62.5°	19.4
65°	17.1
67.5°	14.7
70°	12.4
72.5°	10.1
75°	8.5
77.5°	7.0
80°	5.4
82.5°	3.9
85°	2.3
87.5°	0.8



TEST NUMBER: P1296579  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLD1MW\_3500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)