

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294744

Luminaire Tested: P3AS09R65W2N902750DE010 E3D1H_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294744
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65W2N902750DE010 E3D1H_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 695.0 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294744

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3D1H_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294744

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3D1H_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82			
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77			
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	186235
5°	172925
10°	167220
15°	161159
20°	148996
25°	135734
30°	104877
35°	60793
40°	24131
45°	10265
50°	2422
55°	344
60°	263
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10265 cd/sqm



TEST NUMBER: P1294744

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3D1H_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.1	10.7
10°-20°	197.8	28.5
20°-30°	250.3	36.0
30°-40°	142.6	20.5
40°-50°	28.3	4.1
50°-60°	1.5	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	522.2	75.1
0°-40°	664.8	95.6
0°-60°	694.6	99.9
0°-90°	695.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	695.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	849	
5°	786	74
15°	710	198
25°	561	250
35°	227	143
45°	33	28
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1294744

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3D1H_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	849.3
1°	843.0
2°	829.3
3°	813.3
4°	797.6
5°	785.6
6°	776.7
7°	769.6
8°	763.3
9°	757.0
10°	751.0
11°	744.4
12°	737.6
13°	729.3
14°	720.4
15°	709.9
16°	697.3
17°	683.6
18°	668.7
19°	653.0
20°	638.5
21°	623.6
22°	610.2
23°	596.2
24°	579.9
25°	561.0
26°	538.5
27°	511.3
28°	480.8
29°	448.2
30°	414.2
31°	376.8
32°	339.7
32.5°	320.5
33°	301.9
34°	264.2
35°	227.1
36°	192.8
37°	158.8
37.5°	141.4
38°	127.4
39°	103.1
40°	84.3
42.5°	52.0
45°	33.1



TEST NUMBER: P1294744

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3D1H_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	19.4
50°	7.1
52.5°	1.4
55°	0.9
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)