

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296611

Luminaire Tested: P3AS13R30W2N902765DE010 E3DLP1LI_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296611
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30W2N902765DE010 E3DLP1LI_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 497.0 lumens
Efficiency: N/A
Efficacy: 40.4 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296611
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLP1LI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296611

CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLP1LI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	13.8
10°-20°	148.8	29.9
20°-30°	135.4	27.2
30°-40°	81.8	16.5
40°-50°	32.8	6.6
50°-60°	14.5	2.9
60°-70°	8.8	1.8
70°-80°	4.8	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	352.9	71.0
0°-40°	434.7	87.5
0°-60°	482.1	97.0
0°-90°	497.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	497.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	774	
5°	748	69
15°	540	149
25°	294	135
35°	129	82
45°	40	33
55°	16	15
65°	8	9
75°	5	5
85°	2	1
90°	0	



TEST NUMBER: P1296611
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLP1LI_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	774.5
1°	773.7
2°	770.7
3°	765.3
4°	757.6
5°	747.5
6°	735.2
7°	722.1
8°	705.1
9°	685.9
10°	665.8
11°	642.7
12°	618.1
13°	593.4
14°	566.4
15°	540.2
17.5°	471.6
20°	406.9
22.5°	346.8
25°	294.4
27.5°	246.6
30°	204.2
32.5°	164.9
35°	128.7
37.5°	98.6
40°	74.0
42.5°	53.9
45°	40.1
47.5°	30.1
50°	22.3
52.5°	17.7
55°	16.2
57.5°	13.9
60°	12.3
62.5°	10.0
65°	8.5
67.5°	7.7
70°	6.2
72.5°	5.4
75°	4.6
77.5°	3.9
80°	2.3
82.5°	1.5
85°	1.5
87.5°	0.8



TEST NUMBER: P1296611
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLP1LI_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)