

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294814

Luminaire Tested: P3AS09R65W2N902750DE010 E3DLD1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65W2N902750DE010 E3DLD1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 459.0 lumens
Efficiency: N/A
Efficacy: 51.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294814
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLD1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294814
 CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	81682
5°	80585
10°	77888
15°	73440
20°	67743
25°	61504
30°	54464
35°	46338
40°	36869
45°	26018
50°	15113
55°	8258
60°	7675
65°	6953
70°	6347
75°	5931
80°	5177
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26018 cd/sqm



TEST NUMBER: P1294814

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.4	7.5
10°-20°	90.5	19.7
20°-30°	116.3	25.3
30°-40°	107.6	23.4
40°-50°	64.9	14.1
50°-60°	22.2	4.8
60°-70°	13.4	2.9
70°-80°	7.5	1.6
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	241.3	52.6
0°-40°	348.9	76.0
0°-60°	436.0	95.0
0°-90°	459.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	459.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	372	
5°	366	34
15°	324	91
25°	254	116
35°	173	108
45°	84	65
55°	22	22
65°	13	13
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P1294814
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLD1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	372.5
2.5°	370.7
5°	366.1
7.5°	359.1
10°	349.8
12.5°	338.1
15°	323.5
17.5°	307.8
20°	290.3
22.5°	272.2
25°	254.2
27.5°	234.9
30°	215.1
32.5°	195.3
35°	173.1
37.5°	151.6
40°	128.8
42.5°	106.1
45°	83.9
47.5°	63.5
50°	44.3
52.5°	28.0
55°	21.6
57.5°	19.2
60°	17.5
62.5°	15.2
65°	13.4
67.5°	11.7
70°	9.9
72.5°	8.7
75°	7.0
77.5°	5.8
80°	4.1
82.5°	2.9
85°	1.7
87.5°	1.2
90°	0.0

(END OF REPORT)