

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294825

Luminaire Tested: P3AS09R65W2N902750DE010 E3DLD1WMH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294825
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65W2N902750DE010 E3DLD1WMH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3500K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 466.0 lumens
Efficiency: N/A
Efficacy: 51.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294825
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLD1WMH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1294825

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLD1WMH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82932
5°	81818
10°	79068
15°	74575
20°	68769
25°	62423
30°	55300
35°	47060
40°	37442
45°	26421
50°	15351
55°	8372
60°	7806
65°	7057
70°	6475
75°	6015
80°	5177
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26421 cd/sqm



TEST NUMBER: P1294825

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLD1WMH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.0	7.5
10°-20°	91.9	19.7
20°-30°	118.1	25.3
30°-40°	109.3	23.4
40°-50°	65.9	14.2
50°-60°	22.5	4.8
60°-70°	13.5	2.9
70°-80°	7.6	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	245.0	52.6
0°-40°	354.2	76.0
0°-60°	442.7	95.0
0°-90°	466.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	466.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	378	
5°	372	35
15°	328	92
25°	258	118
35°	176	109
45°	85	66
55°	22	22
65°	14	14
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P1294825

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLD1WMH_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	378.2
2.5°	376.4
5°	371.7
7.5°	364.6
10°	355.1
12.5°	343.3
15°	328.5
17.5°	312.5
20°	294.7
22.5°	276.4
25°	258.0
27.5°	238.5
30°	218.4
32.5°	198.3
35°	175.8
37.5°	153.9
40°	130.8
42.5°	107.7
45°	85.2
47.5°	64.5
50°	45.0
52.5°	28.4
55°	21.9
57.5°	19.5
60°	17.8
62.5°	15.4
65°	13.6
67.5°	11.8
70°	10.1
72.5°	8.9
75°	7.1
77.5°	5.9
80°	4.1
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)