

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296705

Luminaire Tested: P3AS13R35W2N902750DE010 E3DL1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296705
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35W2N902750DE010 E3DL1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 496.0 lumens
Efficiency: N/A
Efficacy: 40.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296705
CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DL1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296705

CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DL1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 |
| 1 | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 96 | 95 | 93 | | | | 93 |
| 2 | 107 | 102 | 98 | 94 | 105 | 100 | 97 | 93 | 97 | 94 | 91 | 94 | 92 | 89 | 91 | 89 | 87 | 86 | | | | 86 |
| 3 | 102 | 95 | 90 | 86 | 100 | 94 | 89 | 85 | 91 | 87 | 84 | 89 | 85 | 82 | 86 | 84 | 81 | 80 | | | | 80 |
| 4 | 97 | 89 | 83 | 79 | 95 | 88 | 82 | 78 | 86 | 81 | 77 | 84 | 80 | 77 | 82 | 78 | 76 | 74 | | | | 74 |
| 5 | 92 | 83 | 77 | 73 | 90 | 82 | 77 | 73 | 81 | 76 | 72 | 79 | 75 | 71 | 77 | 74 | 71 | 69 | | | | 69 |
| 6 | 87 | 78 | 72 | 68 | 86 | 77 | 72 | 68 | 76 | 71 | 67 | 75 | 70 | 67 | 73 | 69 | 66 | 65 | | | | 65 |
| 7 | 83 | 74 | 68 | 63 | 82 | 73 | 67 | 63 | 72 | 67 | 63 | 71 | 66 | 63 | 69 | 65 | 62 | 61 | | | | 61 |
| 8 | 79 | 70 | 64 | 60 | 78 | 69 | 63 | 59 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 59 | 57 | | | | 57 |
| 9 | 76 | 66 | 60 | 56 | 75 | 66 | 60 | 56 | 65 | 59 | 56 | 64 | 59 | 56 | 63 | 59 | 56 | 54 | | | | 54 |
| 10 | 72 | 63 | 57 | 53 | 71 | 62 | 57 | 53 | 61 | 56 | 53 | 61 | 56 | 53 | 60 | 56 | 53 | 51 | | | | 51 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 159417 |
| 5° | 155492 |
| 10° | 142171 |
| 15° | 120659 |
| 20° | 95512 |
| 25° | 72246 |
| 30° | 52590 |
| 35° | 35576 |
| 40° | 21870 |
| 45° | 12559 |
| 50° | 7539 |
| 55° | 6117 |
| 60° | 5350 |
| 65° | 4774 |
| 70° | 3911 |
| 75° | 3897 |
| 80° | 3915 |
| 85° | 3774 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12559 cd/sqm



TEST NUMBER: P1296705

CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DL1WH_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 65.3 | 13.2 |
| 10°-20° | 146.5 | 29.5 |
| 20°-30° | 137.1 | 27.6 |
| 30°-40° | 83.9 | 16.9 |
| 40°-50° | 33.1 | 6.7 |
| 50°-60° | 14.5 | 2.9 |
| 60°-70° | 9.1 | 1.8 |
| 70°-80° | 4.8 | 1.0 |
| 80°-90° | 1.7 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 348.9 | 70.3 |
| 0°-40° | 432.8 | 87.3 |
| 0°-60° | 480.4 | 96.9 |
| 0°-90° | 496.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 496.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 727 | |
| 5° | 706 | 65 |
| 15° | 532 | 147 |
| 25° | 299 | 137 |
| 35° | 133 | 84 |
| 45° | 40 | 33 |
| 55° | 16 | 15 |
| 65° | 9 | 9 |
| 75° | 5 | 5 |
| 85° | 2 | 2 |
| 90° | 0 | |



TEST NUMBER: P1296705
CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DL1WH_3000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 727.0 |
| 1° | 727.8 |
| 2° | 725.5 |
| 3° | 720.9 |
| 4° | 714.1 |
| 5° | 706.4 |
| 6° | 696.5 |
| 7° | 685.0 |
| 8° | 671.3 |
| 9° | 656.0 |
| 10° | 638.5 |
| 11° | 620.1 |
| 12° | 600.3 |
| 13° | 578.9 |
| 14° | 555.2 |
| 15° | 531.5 |
| 17.5° | 470.4 |
| 20° | 409.3 |
| 22.5° | 350.5 |
| 25° | 298.6 |
| 27.5° | 250.5 |
| 30° | 207.7 |
| 32.5° | 168.0 |
| 35° | 132.9 |
| 37.5° | 101.6 |
| 40° | 76.4 |
| 42.5° | 55.0 |
| 45° | 40.5 |
| 47.5° | 29.0 |
| 50° | 22.1 |
| 52.5° | 18.3 |
| 55° | 16.0 |
| 57.5° | 13.7 |
| 60° | 12.2 |
| 62.5° | 10.7 |
| 65° | 9.2 |
| 67.5° | 7.6 |
| 70° | 6.1 |
| 72.5° | 5.3 |
| 75° | 4.6 |
| 77.5° | 3.8 |
| 80° | 3.1 |
| 82.5° | 2.3 |
| 85° | 1.5 |
| 87.5° | 0.8 |



TEST NUMBER: P1296705
CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DL1WH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)