

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294830

Luminaire Tested: P3AS09R65W2N902750DE010 E3DLP1GPH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294830  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R65W2N902750DE010 E3DLP1GPH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3500K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 201.0 lumens  
Efficiency: N/A  
Efficacy: 22.3 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294830  
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLP1GPH\_3500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1294830  
 CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLP1GPH\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	21.0	10.5
10°-20°	50.9	25.3
20°-30°	56.3	28.0
30°-40°	40.9	20.3
40°-50°	19.2	9.5
50°-60°	6.5	3.2
60°-70°	3.7	1.9
70°-80°	1.9	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	128.2	63.8
0°-40°	169.1	84.1
0°-60°	194.7	96.9
0°-90°	201.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	201.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	233	
5°	226	21
15°	183	51
25°	124	56
35°	65	41
45°	24	19
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1294830  
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLP1GPH\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	233.0
2.5°	231.5
5°	226.3
7.5°	218.5
10°	208.4
12.5°	196.5
15°	183.1
17.5°	168.7
20°	153.9
22.5°	138.5
25°	123.5
27.5°	108.1
30°	93.0
32.5°	78.5
35°	65.2
37.5°	53.0
40°	42.0
42.5°	32.2
45°	24.1
47.5°	17.4
50°	11.9
52.5°	8.1
55°	6.7
57.5°	5.8
60°	4.9
62.5°	4.3
65°	3.8
67.5°	3.2
70°	2.6
72.5°	2.3
75°	1.7
77.5°	1.4
80°	1.2
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)