

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296730

Luminaire Tested: P3AS13R35W2N902750DE010 E3DLD1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296730
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35W2N902750DE010 E3DLD1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 618.0 lumens
Efficiency: N/A
Efficacy: 50.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296730
CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DLD1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296730
 CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DLD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69		
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59		
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55		
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51		
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48		
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141173
5°	138168
10°	129412
15°	116164
20°	101042
25°	86110
30°	72138
35°	57447
40°	41535
45°	26297
50°	14328
55°	9940
60°	9385
65°	8717
70°	8335
75°	7117
80°	6693
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26297 cd/sqm



TEST NUMBER: P1296730
 CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DLD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.4	9.5
10°-20°	142.4	23.0
20°-30°	163.2	26.4
30°-40°	133.2	21.5
40°-50°	67.1	10.9
50°-60°	24.9	4.0
60°-70°	16.7	2.7
70°-80°	9.3	1.5
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.0	58.9
0°-40°	497.1	80.4
0°-60°	589.2	95.3
0°-90°	618.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	618.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	644	
5°	628	58
15°	512	142
25°	356	163
35°	215	133
45°	85	67
55°	26	25
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1296730
CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DLD1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	643.8
1°	643.0
2°	641.5
3°	638.4
4°	633.9
5°	627.7
6°	620.1
7°	612.5
8°	602.5
9°	592.6
10°	581.2
11°	568.9
12°	556.0
13°	541.5
14°	526.2
15°	511.7
17.5°	472.7
20°	433.0
22.5°	392.5
25°	355.9
27.5°	320.0
30°	284.9
32.5°	249.7
35°	214.6
37.5°	179.5
40°	145.1
42.5°	113.0
45°	84.8
47.5°	61.1
50°	42.0
52.5°	30.5
55°	26.0
57.5°	23.7
60°	21.4
62.5°	19.1
65°	16.8
67.5°	14.5
70°	13.0
72.5°	10.7
75°	8.4
77.5°	6.9
80°	5.3
82.5°	3.8
85°	2.3
87.5°	1.5



TEST NUMBER: P1296730
CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DLD1MW_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)