

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294962

Luminaire Tested: P3AS09R65W2N902765DE010 E3DLD1GPH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294962  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R65W2N902765DE010 E3DLD1GPH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3500K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 228.0 lumens  
Efficiency: N/A  
Efficacy: 25.3 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294962  
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLD1GPH\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1294962  
 CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLD1GPH\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 102 | 100 | 98  | 99  | 97  | 95  | 95  | 94  | 93  | 91  | 91  | 91  | 91  |
| 2   | 105 | 99  | 94  | 90  | 103 | 97  | 93  | 89  | 94  | 90  | 87  | 91  | 88  | 85  | 88  | 86  | 84  | 82  | 82  | 82  | 82  |
| 3   | 99  | 91  | 85  | 80  | 96  | 89  | 84  | 79  | 87  | 82  | 78  | 84  | 80  | 77  | 82  | 78  | 76  | 74  | 74  | 74  | 74  |
| 4   | 92  | 83  | 77  | 72  | 90  | 82  | 76  | 71  | 80  | 75  | 70  | 78  | 73  | 70  | 76  | 72  | 69  | 67  | 67  | 67  | 67  |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 69  | 65  | 74  | 68  | 64  | 72  | 67  | 63  | 71  | 66  | 63  | 61  | 61  | 61  | 61  |
| 6   | 82  | 71  | 64  | 59  | 80  | 70  | 64  | 59  | 69  | 63  | 58  | 67  | 62  | 58  | 66  | 61  | 58  | 56  | 56  | 56  | 56  |
| 7   | 77  | 66  | 59  | 54  | 75  | 65  | 59  | 54  | 64  | 58  | 54  | 63  | 57  | 53  | 61  | 57  | 53  | 51  | 51  | 51  | 51  |
| 8   | 72  | 61  | 55  | 50  | 71  | 61  | 54  | 50  | 60  | 54  | 49  | 59  | 53  | 49  | 58  | 53  | 49  | 47  | 47  | 47  | 47  |
| 9   | 68  | 57  | 51  | 46  | 67  | 57  | 50  | 46  | 56  | 50  | 46  | 55  | 49  | 46  | 54  | 49  | 45  | 44  | 44  | 44  | 44  |
| 10  | 65  | 54  | 47  | 43  | 64  | 53  | 47  | 43  | 52  | 47  | 43  | 52  | 46  | 42  | 51  | 46  | 42  | 41  | 41  | 41  | 41  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 40567 |
| 5°  | 40018 |
| 10° | 38677 |
| 15° | 36481 |
| 20° | 33650 |
| 25° | 30534 |
| 30° | 27042 |
| 35° | 23022 |
| 40° | 18320 |
| 45° | 12932 |
| 50° | 7505  |
| 55° | 4091  |
| 60° | 3815  |
| 65° | 3476  |
| 70° | 3142  |
| 75° | 2965  |
| 80° | 2526  |
| 85° | 2264  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12932 cd/sqm



TEST NUMBER: P1294962

CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLD1GPH\_3500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 17.1   | 7.5       |
| 10°-20°   | 45.0   | 19.7      |
| 20°-30°   | 57.8   | 25.3      |
| 30°-40°   | 53.5   | 23.4      |
| 40°-50°   | 32.3   | 14.2      |
| 50°-60°   | 11.0   | 4.8       |
| 60°-70°   | 6.6    | 2.9       |
| 70°-80°   | 3.7    | 1.6       |
| 80°-90°   | 1.1    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 119.8  | 52.6      |
| 0°-40°    | 173.3  | 76.0      |
| 0°-60°    | 216.6  | 95.0      |
| 0°-90°    | 228.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 228.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 185 |      |
| 5°  | 182 | 17   |
| 15° | 161 | 45   |
| 25° | 126 | 58   |
| 35° | 86  | 53   |
| 45° | 42  | 32   |
| 55° | 11  | 11   |
| 65° | 7   | 7    |
| 75° | 4   | 4    |
| 85° | 1   | 1    |
| 90° | 0   |      |



TEST NUMBER: P1294962  
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLD1GPH\_3500K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 185.0 |
| 2.5°  | 184.2 |
| 5°    | 181.8 |
| 7.5°  | 178.4 |
| 10°   | 173.7 |
| 12.5° | 167.9 |
| 15°   | 160.7 |
| 17.5° | 152.9 |
| 20°   | 144.2 |
| 22.5° | 135.2 |
| 25°   | 126.2 |
| 27.5° | 116.7 |
| 30°   | 106.8 |
| 32.5° | 97.0  |
| 35°   | 86.0  |
| 37.5° | 75.3  |
| 40°   | 64.0  |
| 42.5° | 52.7  |
| 45°   | 41.7  |
| 47.5° | 31.6  |
| 50°   | 22.0  |
| 52.5° | 13.9  |
| 55°   | 10.7  |
| 57.5° | 9.6   |
| 60°   | 8.7   |
| 62.5° | 7.5   |
| 65°   | 6.7   |
| 67.5° | 5.8   |
| 70°   | 4.9   |
| 72.5° | 4.3   |
| 75°   | 3.5   |
| 77.5° | 2.9   |
| 80°   | 2.0   |
| 82.5° | 1.4   |
| 85°   | 0.9   |
| 87.5° | 0.6   |
| 90°   | 0.0   |

(END OF REPORT)