

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294988

Luminaire Tested: P3AS09R65W2N902765DE010 E3DLD1WH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294988  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R65W2N902765DE010 E3DLD1WH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 463.0 lumens  
Efficiency: N/A  
Efficacy: 51.4 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294988  
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLD1WH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1294988  
 CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLD1WH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	82384
5°	81290
10°	78556
15°	74075
20°	68326
25°	62036
30°	54945
35°	46739
40°	37213
45°	26266
50°	15249
55°	8334
60°	7719
65°	7005
70°	6411
75°	6015
80°	5177
85°	4529

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 26266 cd/sqm



TEST NUMBER: P1294988

CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLD1WH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	34.7	7.5
10°-20°	91.3	19.7
20°-30°	117.3	25.3
30°-40°	108.6	23.4
40°-50°	65.5	14.2
50°-60°	22.4	4.8
60°-70°	13.5	2.9
70°-80°	7.6	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	243.4	52.6
0°-40°	351.9	76.0
0°-60°	439.8	95.0
0°-90°	463.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	463.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	376	
5°	369	35
15°	326	91
25°	256	117
35°	175	109
45°	85	66
55°	22	22
65°	14	13
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P1294988  
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLD1WH\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	375.7
2.5°	374.0
5°	369.3
7.5°	362.2
10°	352.8
12.5°	341.0
15°	326.3
17.5°	310.5
20°	292.8
22.5°	274.6
25°	256.4
27.5°	237.0
30°	217.0
32.5°	197.0
35°	174.6
37.5°	152.9
40°	130.0
42.5°	107.0
45°	84.7
47.5°	64.1
50°	44.7
52.5°	28.2
55°	21.8
57.5°	19.4
60°	17.6
62.5°	15.3
65°	13.5
67.5°	11.8
70°	10.0
72.5°	8.8
75°	7.1
77.5°	5.9
80°	4.1
82.5°	2.9
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)