

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295026

Luminaire Tested: P3AS09R65W2N902765DE010 E3DLP1WMH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1295026  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R65W2N902765DE010 E3DLP1WMH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,  
E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 366.0 lumens  
Efficiency: N/A  
Efficacy: 40.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295026  
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLP1WMH\_2700K

### Luminous Intensity Polar Plot







TEST NUMBER: P1295026

CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLP1WMH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.3	10.5
10°-20°	92.7	25.3
20°-30°	102.5	28.0
30°-40°	74.4	20.3
40°-50°	34.9	9.5
50°-60°	11.7	3.2
60°-70°	6.8	1.9
70°-80°	3.5	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	233.5	63.8
0°-40°	307.9	84.1
0°-60°	354.5	96.9
0°-90°	366.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	366.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	424	
5°	412	38
15°	334	93
25°	225	102
35°	119	74
45°	44	35
55°	12	12
65°	7	7
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1295026  
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLP1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	424.3
2.5°	421.6
5°	412.1
7.5°	397.9
10°	379.4
12.5°	357.8
15°	333.5
17.5°	307.1
20°	280.2
22.5°	252.2
25°	224.8
27.5°	196.8
30°	169.4
32.5°	143.0
35°	118.7
37.5°	96.6
40°	76.5
42.5°	58.6
45°	43.8
47.5°	31.7
50°	21.6
52.5°	14.8
55°	12.1
57.5°	10.6
60°	9.0
62.5°	7.9
65°	6.9
67.5°	5.8
70°	4.7
72.5°	4.2
75°	3.2
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)