

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296908

Luminaire Tested: P3AS13R35W2N902765DE010 E3DLP1GPH\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296908  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R35W2N902765DE010 E3DLP1GPH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 6500K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 245.0 lumens  
Efficiency: N/A  
Efficacy: 19.9 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296908  
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLP1GPH\_6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296908  
 CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLP1GPH\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	78744
5°	76799
10°	70228
15°	59614
20°	47184
25°	35688
30°	25979
35°	17561
40°	10792
45°	6202
50°	3718
55°	3020
60°	2631
65°	2335
70°	1923
75°	1949
80°	1894
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6202 cd/sqm



TEST NUMBER: P1296908

CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLP1GPH\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	32.2	13.2
10°-20°	72.4	29.5
20°-30°	67.7	27.6
30°-40°	41.4	16.9
40°-50°	16.3	6.7
50°-60°	7.2	2.9
60°-70°	4.5	1.8
70°-80°	2.4	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	172.3	70.3
0°-40°	213.8	87.3
0°-60°	237.3	96.9
0°-90°	245.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	245.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	359	
5°	349	32
15°	263	72
25°	148	68
35°	66	41
45°	20	16
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1296908  
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLP1GPH\_6500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	359.1
1°	359.5
2°	358.4
3°	356.1
4°	352.7
5°	348.9
6°	344.0
7°	338.4
8°	331.6
9°	324.0
10°	315.4
11°	306.3
12°	296.5
13°	285.9
14°	274.2
15°	262.6
17.5°	232.4
20°	202.2
22.5°	173.2
25°	147.5
27.5°	123.7
30°	102.6
32.5°	83.0
35°	65.6
37.5°	50.2
40°	37.7
42.5°	27.2
45°	20.0
47.5°	14.3
50°	10.9
52.5°	9.1
55°	7.9
57.5°	6.8
60°	6.0
62.5°	5.3
65°	4.5
67.5°	3.8
70°	3.0
72.5°	2.6
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4



TEST NUMBER: P1296908  
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DLP1GPH\_6500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)