

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295140

Luminaire Tested: P3AS09R70W2N902750DE010 E3DLP1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295140
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70W2N902750DE010 E3DLP1WH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 4000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 596.0 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295140
CATALOG NUMBER: P3AS09R70W2N902750DE010 E3DLP1WH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295140

CATALOG NUMBER: P3AS09R70W2N902750DE010 E3DLP1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92	
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84	
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77	
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70	
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65	
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60	
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55	
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51	
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48	
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115385
5°	113999
10°	110708
15°	106017
20°	99315
25°	90223
30°	77936
35°	62105
40°	45228
45°	29740
50°	13919
55°	4282
60°	4166
65°	3995
70°	3783
75°	3982
80°	3788
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29740 cd/sqm



TEST NUMBER: P1295140

CATALOG NUMBER: P3AS09R70W2N902750DE010 E3DLP1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.8	8.2
10°-20°	130.7	21.9
20°-30°	169.9	28.5
30°-40°	144.1	24.2
40°-50°	74.3	12.5
50°-60°	14.3	2.4
60°-70°	7.8	1.3
70°-80°	4.8	0.8
80°-90°	1.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	349.3	58.6
0°-40°	493.5	82.8
0°-60°	582.1	97.7
0°-90°	596.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	596.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	526	
5°	518	49
15°	467	131
25°	373	170
35°	232	144
45°	96	74
55°	11	14
65°	8	8
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1295140
CATALOG NUMBER: P3AS09R70W2N902750DE010 E3DLP1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	526.2
2.5°	524.4
5°	517.9
7.5°	508.4
10°	497.2
12.5°	483.0
15°	467.0
17.5°	447.5
20°	425.6
22.5°	400.7
25°	372.9
27.5°	341.5
30°	307.8
32.5°	270.5
35°	232.0
37.5°	194.1
40°	158.0
42.5°	124.3
45°	95.9
47.5°	70.4
50°	40.8
52.5°	17.8
55°	11.2
57.5°	10.7
60°	9.5
62.5°	8.9
65°	7.7
67.5°	7.1
70°	5.9
72.5°	5.3
75°	4.7
77.5°	3.6
80°	3.0
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)