

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295182

Luminaire Tested: P3AS09R70W2N902765DE010 E3CD1MMS_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295182
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70W2N902765DE010 E3CD1MMS_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 729.0 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295182
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3CD1MMS_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295182
 CATALOG NUMBER: P3AS09R70W2N902765DE010 E3CD1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94		93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87		85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80		78
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74		72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68		66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63		61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58		57
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54		53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50		49
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	144769
5°	138124
10°	131416
15°	127901
20°	123187
25°	116595
30°	108447
35°	91096
40°	58710
45°	27290
50°	7164
55°	1797
60°	1798
65°	1505
70°	1475
75°	1440
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27290 cd/sqm



TEST NUMBER: P1295182

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3CD1MMS_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.7	8.1
10°-20°	158.3	21.7
20°-30°	221.2	30.3
30°-40°	205.1	28.1
40°-50°	73.5	10.1
50°-60°	6.3	0.9
60°-70°	3.1	0.4
70°-80°	2.0	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	438.3	60.1
0°-40°	643.4	88.3
0°-60°	723.1	99.2
0°-90°	729.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	729.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	660	
5°	628	59
15°	563	158
25°	482	221
35°	340	205
45°	88	74
55°	5	6
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1295182
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3CD1MMS_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	660.2
2.5°	650.3
5°	627.5
7.5°	606.6
10°	590.2
12.5°	576.8
15°	563.4
17.5°	547.1
20°	527.9
22.5°	505.8
25°	481.9
27.5°	457.4
30°	428.3
32.5°	391.0
35°	340.3
37.5°	275.6
40°	205.1
42.5°	139.8
45°	88.0
47.5°	48.9
50°	21.0
52.5°	7.0
55°	4.7
57.5°	4.1
60°	4.1
62.5°	3.5
65°	2.9
67.5°	2.9
70°	2.3
72.5°	2.3
75°	1.7
77.5°	1.7
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)