

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295204

Luminaire Tested: P3AS09R70W2N902765DE010 E3D1LI_6500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295204
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70W2N902765DE010 E3D1LI_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 6500K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 702.0 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295204
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1LI_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1295204

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1LI_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 96 | 95 | 93 | | | 93 |
| 2 | 107 | 102 | 98 | 94 | 105 | 100 | 96 | 93 | 97 | 94 | 91 | 94 | 91 | 89 | 91 | 89 | 87 | 85 | | | 85 |
| 3 | 101 | 94 | 89 | 85 | 99 | 93 | 88 | 84 | 90 | 86 | 83 | 88 | 84 | 81 | 86 | 83 | 80 | 79 | | | 79 |
| 4 | 95 | 87 | 81 | 77 | 94 | 86 | 81 | 77 | 84 | 79 | 76 | 82 | 78 | 75 | 80 | 77 | 74 | 72 | | | 72 |
| 5 | 90 | 81 | 75 | 70 | 88 | 80 | 74 | 70 | 78 | 73 | 69 | 77 | 72 | 69 | 75 | 71 | 68 | 66 | | | 66 |
| 6 | 85 | 75 | 69 | 64 | 83 | 75 | 69 | 64 | 73 | 68 | 64 | 72 | 67 | 63 | 70 | 66 | 63 | 61 | | | 61 |
| 7 | 80 | 70 | 64 | 59 | 79 | 70 | 63 | 59 | 68 | 63 | 59 | 67 | 62 | 58 | 66 | 61 | 58 | 57 | | | 57 |
| 8 | 76 | 66 | 59 | 55 | 75 | 65 | 59 | 55 | 64 | 58 | 54 | 63 | 58 | 54 | 62 | 57 | 54 | 52 | | | 52 |
| 9 | 72 | 61 | 55 | 51 | 71 | 61 | 55 | 51 | 60 | 54 | 50 | 59 | 54 | 50 | 58 | 53 | 50 | 49 | | | 49 |
| 10 | 68 | 58 | 51 | 47 | 67 | 57 | 51 | 47 | 56 | 51 | 47 | 55 | 50 | 47 | 55 | 50 | 47 | 45 | | | 45 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 136502 |
| 5° | 128703 |
| 10° | 122042 |
| 15° | 119842 |
| 20° | 115510 |
| 25° | 108901 |
| 30° | 108118 |
| 35° | 94174 |
| 40° | 60914 |
| 45° | 28778 |
| 50° | 4025 |
| 55° | 344 |
| 60° | 263 |
| 65° | 311 |
| 70° | 192 |
| 75° | 254 |
| 80° | 379 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 28778 cd/sqm



TEST NUMBER: P1295204

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1LI_6500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 54.6 | 7.8 |
| 10°-20° | 148.3 | 21.1 |
| 20°-30° | 209.7 | 29.9 |
| 30°-40° | 210.8 | 30.0 |
| 40°-50° | 75.8 | 10.8 |
| 50°-60° | 2.0 | 0.3 |
| 60°-70° | 0.5 | 0.1 |
| 70°-80° | 0.3 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 412.6 | 58.8 |
| 0°-40° | 623.4 | 88.8 |
| 0°-60° | 701.2 | 99.9 |
| 0°-90° | 702.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 702.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 622 | |
| 5° | 585 | 55 |
| 15° | 528 | 148 |
| 25° | 450 | 210 |
| 35° | 352 | 211 |
| 45° | 93 | 76 |
| 55° | 1 | 2 |
| 65° | 1 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1295204

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1LI_6500K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 622.5 |
| 1° | 620.8 |
| 2° | 615.3 |
| 3° | 606.6 |
| 4° | 595.7 |
| 5° | 584.7 |
| 6° | 574.3 |
| 7° | 566.3 |
| 8° | 559.1 |
| 9° | 553.3 |
| 10° | 548.1 |
| 11° | 543.8 |
| 12° | 539.7 |
| 13° | 535.7 |
| 14° | 532.0 |
| 15° | 527.9 |
| 16° | 523.0 |
| 17° | 517.8 |
| 18° | 511.5 |
| 19° | 503.7 |
| 20° | 495.0 |
| 21° | 485.5 |
| 22° | 476.0 |
| 23° | 466.8 |
| 24° | 457.9 |
| 25° | 450.1 |
| 26° | 444.6 |
| 27° | 440.3 |
| 28° | 436.8 |
| 29° | 432.8 |
| 30° | 427.0 |
| 31° | 418.6 |
| 32° | 406.8 |
| 32.5° | 400.2 |
| 33° | 391.3 |
| 34° | 373.7 |
| 35° | 351.8 |
| 36° | 327.5 |
| 37° | 300.1 |
| 37.5° | 287.5 |
| 38° | 270.2 |
| 39° | 239.3 |
| 40° | 212.8 |
| 42.5° | 147.3 |
| 45° | 92.8 |



TEST NUMBER: P1295204

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1LI_6500K

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|------|
| 47.5° | 49.9 |
| 50° | 11.8 |
| 52.5° | 1.4 |
| 55° | 0.9 |
| 57.5° | 0.9 |
| 60° | 0.6 |
| 62.5° | 0.6 |
| 65° | 0.6 |
| 67.5° | 0.3 |
| 70° | 0.3 |
| 72.5° | 0.3 |
| 75° | 0.3 |
| 77.5° | 0.3 |
| 80° | 0.3 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)