

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297031

Luminaire Tested: P3AS13R40W2N902750DE010 E3DL1MW\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297031  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R40W2N902750DE010 E3DL1MW\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 90CRI ,  
E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 899.0 lumens  
Efficiency: N/A  
Efficacy: 73.1 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297031  
CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DL1MW\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1297031

CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DL1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	96	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	81	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	67	67	67	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	64	64	64	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	61	61	61	60

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	397797
5°	386242
10°	350495
15°	289559
20°	208875
25°	129201
30°	69935
35°	36138
40°	19665
45°	11009
50°	5526
55°	4129
60°	3728
65°	3580
70°	3462
75°	3304
80°	2904
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11009 cd/sqm



TEST NUMBER: P1297031

CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DL1MW\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	161.7	18.0
10°-20°	347.3	38.6
20°-30°	247.9	27.6
30°-40°	91.2	10.1
40°-50°	28.7	3.2
50°-60°	10.0	1.1
60°-70°	6.9	0.8
70°-80°	4.1	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	756.9	84.2
0°-40°	848.2	94.3
0°-60°	886.9	98.7
0°-90°	899.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	899.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1814	
5°	1755	162
15°	1276	347
25°	534	248
35°	135	91
45°	36	29
55°	11	10
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1297031  
CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DL1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1814.1
2.5°	1800.2
5°	1754.7
7.5°	1679.1
10°	1574.1
12.5°	1440.6
15°	1275.5
17.5°	1090.3
20°	895.1
22.5°	703.0
25°	534.0
27.5°	392.0
30°	276.2
32.5°	193.7
35°	135.0
37.5°	95.7
40°	68.7
42.5°	49.4
45°	35.5
47.5°	23.9
50°	16.2
52.5°	11.6
55°	10.8
57.5°	10.0
60°	8.5
62.5°	7.7
65°	6.9
67.5°	6.2
70°	5.4
72.5°	4.6
75°	3.9
77.5°	3.1
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)