

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295219

Luminaire Tested: P3AS09R70W2N902765DE010 E3D1WMH_3500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295219
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70W2N902765DE010 E3D1WMH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3500K CCT AND, 90CRI ,
E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 706.1 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295219
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1WMH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1295219

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1WMH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.9	7.8
10°-20°	149.1	21.1
20°-30°	210.9	29.9
30°-40°	212.0	30.0
40°-50°	76.3	10.8
50°-60°	2.1	0.3
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	414.9	58.8
0°-40°	626.9	88.8
0°-60°	705.2	99.9
0°-90°	706.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	706.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	626	
5°	588	55
15°	531	149
25°	453	211
35°	354	212
45°	93	76
55°	1	2
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1295219
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1WMH_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	626.0
1°	624.3
2°	618.8
3°	610.1
4°	599.1
5°	588.0
6°	577.6
7°	569.5
8°	562.2
9°	556.4
10°	551.2
11°	546.9
12°	542.8
13°	538.8
14°	535.0
15°	530.9
16°	526.0
17°	520.8
18°	514.4
19°	506.6
20°	497.9
21°	488.3
22°	478.7
23°	469.5
24°	460.5
25°	452.6
26°	447.1
27°	442.8
28°	439.3
29°	435.2
30°	429.4
31°	421.0
32°	409.1
32.5°	402.5
33°	393.5
34°	375.8
35°	353.8
36°	329.4
37°	301.9
37.5°	289.1
38°	271.7
39°	240.7
40°	214.0
42.5°	148.2
45°	93.4



TEST NUMBER: P1295219
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3D1WMH_3500K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	50.2
50°	11.9
52.5°	1.4
55°	0.9
57.5°	0.9
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)