

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295224

Luminaire Tested: P3AS09R70W2N902765DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295224
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70W2N902765DE010 E3DL1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 288.0 lumens
Efficiency: N/A
Efficacy: 32.0 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295224
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295224

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55763
5°	55096
10°	53484
15°	51238
20°	47978
25°	43599
30°	37651
35°	30008
40°	21870
45°	14358
50°	6720
55°	2064
60°	2017
65°	1920
70°	1859
75°	1949
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14358 cd/sqm



TEST NUMBER: P1295224

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.6	8.2
10°-20°	63.2	21.9
20°-30°	82.1	28.5
30°-40°	69.6	24.2
40°-50°	35.9	12.5
50°-60°	6.9	2.4
60°-70°	3.7	1.3
70°-80°	2.3	0.8
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	168.8	58.6
0°-40°	238.4	82.8
0°-60°	281.3	97.7
0°-90°	288.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	288.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	254	
5°	250	24
15°	226	63
25°	180	82
35°	112	70
45°	46	36
55°	5	7
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1295224
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	254.3
2.5°	253.4
5°	250.3
7.5°	245.7
10°	240.2
12.5°	233.4
15°	225.7
17.5°	216.2
20°	205.6
22.5°	193.6
25°	180.2
27.5°	165.0
30°	148.7
32.5°	130.7
35°	112.1
37.5°	93.8
40°	76.4
42.5°	60.1
45°	46.3
47.5°	34.0
50°	19.7
52.5°	8.6
55°	5.4
57.5°	5.1
60°	4.6
62.5°	4.3
65°	3.7
67.5°	3.4
70°	2.9
72.5°	2.6
75°	2.3
77.5°	1.7
80°	1.4
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)