

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295242

Luminaire Tested: P3AS09R70W2N902765DE010 E3DL1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295242
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70W2N902765DE010 E3DL1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 587.0 lumens
Efficiency: N/A
Efficacy: 65.2 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295242
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3DL1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295242

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3DL1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77				77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70				70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65				65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60				60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55				55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44				44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113631
5°	112282
10°	109038
15°	104405
20°	97799
25°	88868
30°	76746
35°	61168
40°	44541
45°	29274
50°	13714
55°	4244
60°	4079
65°	3943
70°	3719
75°	3982
80°	3662
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29274 cd/sqm



TEST NUMBER: P1295242

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3DL1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.0	8.2
10°-20°	128.7	21.9
20°-30°	167.3	28.5
30°-40°	142.0	24.2
40°-50°	73.2	12.5
50°-60°	14.1	2.4
60°-70°	7.6	1.3
70°-80°	4.7	0.8
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	344.1	58.6
0°-40°	486.0	82.8
0°-60°	573.3	97.7
0°-90°	587.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	587.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	518	
5°	510	48
15°	460	129
25°	367	167
35°	228	142
45°	94	73
55°	11	14
65°	8	8
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1295242
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3DL1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	518.2
2.5°	516.5
5°	510.1
7.5°	500.7
10°	489.7
12.5°	475.7
15°	459.9
17.5°	440.7
20°	419.1
22.5°	394.6
25°	367.3
27.5°	336.4
30°	303.1
32.5°	266.4
35°	228.5
37.5°	191.2
40°	155.6
42.5°	122.4
45°	94.4
47.5°	69.4
50°	40.2
52.5°	17.5
55°	11.1
57.5°	10.5
60°	9.3
62.5°	8.7
65°	7.6
67.5°	7.0
70°	5.8
72.5°	5.2
75°	4.7
77.5°	3.5
80°	2.9
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)