

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297065

Luminaire Tested: P3AS13R40W2N902750DE010 E3DLD1WH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297065  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R40W2N902750DE010 E3DLD1WH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 4000K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 693.0 lumens  
Efficiency: N/A  
Efficacy: 56.3 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297065  
CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLD1WH\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1297065  
 CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLD1WH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	155558
5°	152740
10°	143974
15°	130784
20°	114880
25°	98111
30°	81278
35°	62694
40°	44598
45°	30050
50°	16409
55°	11546
60°	10876
65°	10066
70°	8976
75°	8557
80°	6819
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 30050 cd/sqm



TEST NUMBER: P1297065  
 CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLD1WH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.7	9.3
10°-20°	160.5	23.2
20°-30°	185.5	26.8
30°-40°	146.2	21.1
40°-50°	75.1	10.8
50°-60°	28.7	4.1
60°-70°	19.0	2.7
70°-80°	10.3	1.5
80°-90°	3.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	410.7	59.3
0°-40°	556.9	80.4
0°-60°	660.6	95.3
0°-90°	693.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	693.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	709	
5°	694	65
15°	576	160
25°	406	186
35°	234	146
45°	97	75
55°	30	29
65°	19	19
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P1297065  
CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLD1WH\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	709.4
2.5°	705.6
5°	693.9
7.5°	673.8
10°	646.6
12.5°	614.8
15°	576.1
17.5°	535.8
20°	492.3
22.5°	448.1
25°	405.5
27.5°	362.9
30°	321.0
32.5°	278.3
35°	234.2
37.5°	193.1
40°	155.8
42.5°	124.1
45°	96.9
47.5°	70.6
50°	48.1
52.5°	34.9
55°	30.2
57.5°	27.1
60°	24.8
62.5°	21.7
65°	19.4
67.5°	16.3
70°	14.0
72.5°	11.6
75°	10.1
77.5°	7.8
80°	5.4
82.5°	4.7
85°	2.3
87.5°	1.6
90°	0.0

(END OF REPORT)