

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295357

Luminaire Tested: P3AS13R15W2N902750DE010 E3D1WMH_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295357
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R15W2N902750DE010 E3D1WMH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,
E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 895.9 lumens
Efficiency: N/A
Efficacy: 72.8 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295357
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3D1WMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1295357

CATALOG NUMBER: P3AS13R15W2N902750DE010 E3D1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 105 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 98 | 98 | 98 |
| 2 | 112 | 109 | 107 | 105 | 110 | 108 | 105 | 103 | 105 | 103 | 101 | 102 | 100 | 99 | 99 | 98 | 97 | 96 | 96 | 96 | 96 |
| 3 | 110 | 106 | 102 | 100 | 108 | 104 | 102 | 99 | 102 | 100 | 98 | 100 | 98 | 96 | 98 | 96 | 95 | 94 | 94 | 94 | 94 |
| 4 | 107 | 102 | 99 | 96 | 106 | 101 | 98 | 96 | 99 | 97 | 95 | 98 | 96 | 94 | 96 | 94 | 93 | 92 | 92 | 92 | 92 |
| 5 | 105 | 100 | 96 | 94 | 103 | 99 | 96 | 93 | 97 | 94 | 92 | 96 | 93 | 92 | 94 | 93 | 91 | 90 | 90 | 90 | 90 |
| 6 | 102 | 97 | 94 | 91 | 101 | 96 | 93 | 91 | 95 | 92 | 90 | 94 | 92 | 90 | 93 | 91 | 89 | 88 | 88 | 88 | 88 |
| 7 | 100 | 95 | 91 | 89 | 99 | 94 | 91 | 89 | 93 | 90 | 88 | 92 | 90 | 88 | 91 | 89 | 88 | 87 | 87 | 87 | 87 |
| 8 | 98 | 93 | 89 | 87 | 97 | 92 | 89 | 87 | 91 | 89 | 87 | 91 | 88 | 86 | 90 | 88 | 86 | 85 | 85 | 85 | 85 |
| 9 | 96 | 91 | 88 | 85 | 96 | 91 | 87 | 85 | 90 | 87 | 85 | 89 | 87 | 85 | 89 | 86 | 85 | 84 | 84 | 84 | 84 |
| 10 | 95 | 89 | 86 | 84 | 94 | 89 | 86 | 84 | 88 | 85 | 83 | 88 | 85 | 83 | 87 | 85 | 83 | 82 | 82 | 82 | 82 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1706223 |
| 5° | 1391302 |
| 10° | 681372 |
| 15° | 208560 |
| 20° | 88324 |
| 25° | 39946 |
| 30° | 15572 |
| 35° | 7174 |
| 40° | 2233 |
| 45° | 837 |
| 50° | 341 |
| 55° | 115 |
| 60° | 132 |
| 65° | 156 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 837 cd/sqm



TEST NUMBER: P1295357
 CATALOG NUMBER: P3AS13R15W2N902750DE010 E3D1WMH_2700K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 492.0 | 54.9 |
| 10°-20° | 301.9 | 33.7 |
| 20°-30° | 81.1 | 9.1 |
| 30°-40° | 17.8 | 2.0 |
| 40°-50° | 2.5 | 0.3 |
| 50°-60° | 0.4 | 0.0 |
| 60°-70° | 0.2 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 875.0 | 97.7 |
| 0°-40° | 892.8 | 99.7 |
| 0°-60° | 895.7 | 100.0 |
| 0°-90° | 895.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 895.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 7781 | |
| 5° | 6321 | 492 |
| 15° | 919 | 302 |
| 25° | 165 | 81 |
| 35° | 27 | 18 |
| 45° | 3 | 2 |
| 55° | 0 | 0 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1295357
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3D1WMH_2700K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 7781.0 |
| 1° | 7732.4 |
| 2° | 7576.4 |
| 3° | 7295.5 |
| 4° | 6872.5 |
| 5° | 6320.7 |
| 6° | 5696.6 |
| 7° | 5001.5 |
| 8° | 4362.7 |
| 9° | 3685.6 |
| 10° | 3060.1 |
| 11° | 2441.1 |
| 12° | 1878.1 |
| 13° | 1444.6 |
| 14° | 1143.6 |
| 15° | 918.7 |
| 17.5° | 569.4 |
| 20° | 378.5 |
| 22.5° | 254.8 |
| 25° | 165.1 |
| 27.5° | 97.8 |
| 30° | 61.5 |
| 32.5° | 41.4 |
| 35° | 26.8 |
| 37.5° | 14.9 |
| 40° | 7.8 |
| 42.5° | 4.4 |
| 45° | 2.7 |
| 47.5° | 1.7 |
| 50° | 1.0 |
| 52.5° | 0.7 |
| 55° | 0.3 |
| 57.5° | 0.3 |
| 60° | 0.3 |
| 62.5° | 0.3 |
| 65° | 0.3 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |



TEST NUMBER: P1295357
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3D1WMH_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)