

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297305

Luminaire Tested: P3AS13R45W2N902750DE010 E3CD1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45W2N902750DE010 E3CD1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 90CRI ,
E3CD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1034.0 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297305
CATALOG NUMBER: P3AS13R45W2N902750DE010 E3CD1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297305

CATALOG NUMBER: P3AS13R45W2N902750DE010 E3CD1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.1	18.7
10°-20°	443.2	42.9
20°-30°	319.1	30.9
30°-40°	66.4	6.4
40°-50°	6.1	0.6
50°-60°	2.5	0.2
60°-70°	2.0	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	955.4	92.4
0°-40°	1021.8	98.8
0°-60°	1030.3	99.7
0°-90°	1034.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1034.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2044	
5°	2048	193
15°	1612	443
25°	704	319
35°	85	66
45°	5	6
55°	3	3
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1297305

CATALOG NUMBER: P3AS13R45W2N902750DE010 E3CD1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2044.4
2.5°	2045.2
5°	2047.5
7.5°	2032.8
10°	1961.9
12.5°	1813.8
15°	1612.5
17.5°	1406.6
20°	1199.2
22.5°	960.9
25°	704.1
27.5°	464.2
30°	279.9
32.5°	156.5
35°	84.8
37.5°	47.8
40°	24.7
42.5°	10.8
45°	4.6
47.5°	3.1
50°	3.1
52.5°	3.1
55°	3.1
57.5°	2.3
60°	2.3
62.5°	2.3
65°	2.3
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)