

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297356

Luminaire Tested: P3AS13R45W2N902750DE010 E3DLD1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297356
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45W2N902750DE010 E3DLD1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 601.0 lumens
Efficiency: N/A
Efficacy: 48.9 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297356
CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DLD1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1297356
 CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DLD1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			83
3	99	92	86	82	97	90	85	81	88	83	80	85	81	78	83	80	77	75			75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63			63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58			58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54			54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50			50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47			47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44			44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127424
5°	125159
10°	118435
15°	108014
20°	95512
25°	82940
30°	71201
35°	59321
40°	44226
45°	27073
50°	12520
55°	9787
60°	9429
65°	8613
70°	8014
75°	7625
80°	6945
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27073 cd/sqm



TEST NUMBER: P1297356

CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.1	8.8
10°-20°	132.5	22.0
20°-30°	157.4	26.2
30°-40°	136.8	22.8
40°-50°	68.6	11.4
50°-60°	23.8	4.0
60°-70°	16.7	2.8
70°-80°	9.3	1.5
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	343.0	57.1
0°-40°	479.8	79.8
0°-60°	572.1	95.2
0°-90°	601.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	601.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	581	
5°	569	53
15°	476	132
25°	343	157
35°	222	137
45°	87	69
55°	26	24
65°	17	17
75°	9	9
85°	2	3
90°	0	



TEST NUMBER: P1297356
CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	581.1
2.5°	578.3
5°	568.6
7.5°	553.4
10°	531.9
12.5°	505.6
15°	475.8
17.5°	442.6
20°	409.3
22.5°	375.4
25°	342.8
27.5°	311.7
30°	281.2
32.5°	252.1
35°	221.6
37.5°	189.1
40°	154.5
42.5°	120.5
45°	87.3
47.5°	57.5
50°	36.7
52.5°	28.4
55°	25.6
57.5°	23.5
60°	21.5
62.5°	19.4
65°	16.6
67.5°	14.5
70°	12.5
72.5°	10.4
75°	9.0
77.5°	6.9
80°	5.5
82.5°	4.2
85°	2.1
87.5°	1.4
90°	0.0

(END OF REPORT)