

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297373

Luminaire Tested: P3AS13R45W2N902750DE010 E3DLP1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297373
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45W2N902750DE010 E3DLP1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3500K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 274.0 lumens
Efficiency: N/A
Efficacy: 22.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297373
CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DLP1GPH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1297373

CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DLP1GPH_3500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 33.6 | 12.2 |
| 10°-20° | 77.9 | 28.4 |
| 20°-30° | 77.3 | 28.2 |
| 30°-40° | 49.8 | 18.2 |
| 40°-50° | 19.2 | 7.0 |
| 50°-60° | 7.8 | 2.8 |
| 60°-70° | 4.9 | 1.8 |
| 70°-80° | 2.7 | 1.0 |
| 80°-90° | 0.8 | 0.3 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 188.8 | 68.9 |
| 0°-40° | 238.6 | 87.1 |
| 0°-60° | 265.6 | 96.9 |
| 0°-90° | 274.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 274.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 372 | |
| 5° | 362 | 34 |
| 15° | 282 | 78 |
| 25° | 169 | 77 |
| 35° | 79 | 50 |
| 45° | 23 | 19 |
| 55° | 9 | 8 |
| 65° | 5 | 5 |
| 75° | 3 | 3 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P1297373
CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DLP1GPH_3500K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 372.2 |
| 2.5° | 370.3 |
| 5° | 362.3 |
| 7.5° | 348.6 |
| 10° | 330.4 |
| 12.5° | 307.6 |
| 15° | 281.8 |
| 17.5° | 253.7 |
| 20° | 225.2 |
| 22.5° | 196.3 |
| 25° | 169.0 |
| 27.5° | 143.2 |
| 30° | 119.3 |
| 32.5° | 98.4 |
| 35° | 79.4 |
| 37.5° | 62.3 |
| 40° | 46.3 |
| 42.5° | 33.4 |
| 45° | 23.2 |
| 47.5° | 15.6 |
| 50° | 11.4 |
| 52.5° | 9.5 |
| 55° | 8.7 |
| 57.5° | 7.6 |
| 60° | 6.8 |
| 62.5° | 5.7 |
| 65° | 4.9 |
| 67.5° | 4.2 |
| 70° | 3.4 |
| 72.5° | 3.0 |
| 75° | 2.7 |
| 77.5° | 1.9 |
| 80° | 1.5 |
| 82.5° | 1.1 |
| 85° | 0.8 |
| 87.5° | 0.4 |
| 90° | 0.0 |

(END OF REPORT)