

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297374

Luminaire Tested: P3AS13R45W2N902750DE010 E3DLP1GPH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297374  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R45W2N902750DE010 E3DLP1GPH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 274.0 lumens  
Efficiency: N/A  
Efficacy: 22.3 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297374  
CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DLP1GPH\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1297374  
 CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DLP1GPH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 96  | 94  | 93  |    |    |   |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  | 94  | 91  | 89  | 91  | 89  | 87  | 86  |    |    |   |
| 3   | 102 | 95  | 90  | 85  | 100 | 93  | 89  | 85  | 91  | 87  | 83  | 88  | 85  | 82  | 86  | 83  | 81  | 79  |    |    |   |
| 4   | 96  | 88  | 83  | 78  | 94  | 87  | 82  | 78  | 85  | 81  | 77  | 83  | 79  | 76  | 81  | 78  | 75  | 74  |    |    |   |
| 5   | 91  | 83  | 77  | 72  | 90  | 82  | 76  | 72  | 80  | 75  | 71  | 78  | 74  | 71  | 77  | 73  | 70  | 69  |    |    |   |
| 6   | 87  | 78  | 72  | 67  | 85  | 77  | 71  | 67  | 75  | 70  | 66  | 74  | 69  | 66  | 73  | 69  | 66  | 64  |    |    |   |
| 7   | 83  | 73  | 67  | 63  | 81  | 72  | 67  | 63  | 71  | 66  | 62  | 70  | 65  | 62  | 69  | 65  | 61  | 60  |    |    |   |
| 8   | 79  | 69  | 63  | 59  | 77  | 68  | 63  | 59  | 67  | 62  | 58  | 66  | 62  | 58  | 65  | 61  | 58  | 56  |    |    |   |
| 9   | 75  | 65  | 59  | 55  | 74  | 65  | 59  | 55  | 64  | 59  | 55  | 63  | 58  | 55  | 62  | 58  | 55  | 53  |    |    |   |
| 10  | 72  | 62  | 56  | 52  | 71  | 61  | 56  | 52  | 61  | 55  | 52  | 60  | 55  | 52  | 59  | 55  | 52  | 50  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 81616 |
| 5°  | 79749 |
| 10° | 73568 |
| 15° | 63973 |
| 20° | 52551 |
| 25° | 40889 |
| 30° | 30207 |
| 35° | 21255 |
| 40° | 13253 |
| 45° | 7195  |
| 50° | 3889  |
| 55° | 3326  |
| 60° | 2982  |
| 65° | 2542  |
| 70° | 2180  |
| 75° | 2288  |
| 80° | 1894  |
| 85° | 2013  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7195 cd/sqm



TEST NUMBER: P1297374

CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DLP1GPH\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 33.6   | 12.2      |
| 10°-20°   | 77.9   | 28.4      |
| 20°-30°   | 77.3   | 28.2      |
| 30°-40°   | 49.8   | 18.2      |
| 40°-50°   | 19.2   | 7.0       |
| 50°-60°   | 7.8    | 2.8       |
| 60°-70°   | 4.9    | 1.8       |
| 70°-80°   | 2.7    | 1.0       |
| 80°-90°   | 0.8    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 188.8  | 68.9      |
| 0°-40°    | 238.6  | 87.1      |
| 0°-60°    | 265.6  | 96.9      |
| 0°-90°    | 274.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 274.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 372 |      |
| 5°  | 362 | 34   |
| 15° | 282 | 78   |
| 25° | 169 | 77   |
| 35° | 79  | 50   |
| 45° | 23  | 19   |
| 55° | 9   | 8    |
| 65° | 5   | 5    |
| 75° | 3   | 3    |
| 85° | 1   | 1    |
| 90° | 0   |      |



TEST NUMBER: P1297374  
CATALOG NUMBER: P3AS13R45W2N902750DE010 E3DLP1GPH\_4000K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 372.2 |
| 2.5°  | 370.3 |
| 5°    | 362.3 |
| 7.5°  | 348.6 |
| 10°   | 330.4 |
| 12.5° | 307.6 |
| 15°   | 281.8 |
| 17.5° | 253.7 |
| 20°   | 225.2 |
| 22.5° | 196.3 |
| 25°   | 169.0 |
| 27.5° | 143.2 |
| 30°   | 119.3 |
| 32.5° | 98.4  |
| 35°   | 79.4  |
| 37.5° | 62.3  |
| 40°   | 46.3  |
| 42.5° | 33.4  |
| 45°   | 23.2  |
| 47.5° | 15.6  |
| 50°   | 11.4  |
| 52.5° | 9.5   |
| 55°   | 8.7   |
| 57.5° | 7.6   |
| 60°   | 6.8   |
| 62.5° | 5.7   |
| 65°   | 4.9   |
| 67.5° | 4.2   |
| 70°   | 3.4   |
| 72.5° | 3.0   |
| 75°   | 2.7   |
| 77.5° | 1.9   |
| 80°   | 1.5   |
| 82.5° | 1.1   |
| 85°   | 0.8   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)