

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295411

Luminaire Tested: P3AS13R15W2N902750DE010 E3DLD1MW\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1295411  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R15W2N902750DE010 E3DLD1MW\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 5000K CCT AND, 90CRI ,  
E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 609.0 lumens  
Efficiency: N/A  
Efficacy: 49.5 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295411  
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DLD1MW\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1295411

CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DLD1MW\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.6	10.3
10°-20°	146.8	24.1
20°-30°	161.8	26.6
30°-40°	121.1	19.9
40°-50°	62.8	10.3
50°-60°	26.0	4.3
60°-70°	16.1	2.6
70°-80°	9.0	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	371.2	61.0
0°-40°	492.4	80.9
0°-60°	581.2	95.4
0°-90°	609.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	609.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	700	
5°	679	63
15°	527	147
25°	354	162
35°	192	121
45°	79	63
55°	27	26
65°	16	16
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1295411  
CATALOG NUMBER: P3AS13R15W2N902750DE010 E3DLD1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	700.5
1°	701.3
2°	699.0
3°	694.4
4°	687.4
5°	678.9
6°	668.1
7°	656.6
8°	642.7
9°	628.0
10°	613.3
12.5°	570.9
15°	526.9
17.5°	483.0
20°	439.8
22.5°	395.8
25°	354.1
27.5°	312.5
30°	270.8
32.5°	229.9
35°	192.1
37.5°	159.7
40°	130.4
42.5°	103.4
45°	78.7
47.5°	59.4
50°	44.7
52.5°	33.2
55°	27.0
57.5°	23.9
60°	20.8
62.5°	18.5
65°	16.2
67.5°	13.9
70°	12.3
72.5°	10.0
75°	8.5
77.5°	6.9
80°	5.4
82.5°	3.9
85°	2.3
87.5°	0.8
90°	0.0

(END OF REPORT)