

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297453

Luminaire Tested: P3AS13R45W2N902765DE010 E3DL1H_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297453
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45W2N902765DE010 E3DL1H_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 90CRI ,
E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 862.0 lumens
Efficiency: N/A
Efficacy: 70.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297453
CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DL1H_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297453
 CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DL1H_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 | 94 | 94 | 94 |
| 2 | 109 | 104 | 100 | 97 | 106 | 102 | 99 | 96 | 99 | 96 | 94 | 96 | 94 | 92 | 93 | 91 | 90 | 88 | 88 | 88 | 88 |
| 3 | 104 | 98 | 93 | 89 | 102 | 96 | 92 | 88 | 94 | 90 | 87 | 91 | 88 | 86 | 89 | 86 | 84 | 83 | 83 | 83 | 83 |
| 4 | 99 | 92 | 87 | 83 | 97 | 91 | 86 | 82 | 89 | 85 | 81 | 87 | 83 | 80 | 85 | 82 | 79 | 78 | 78 | 78 | 78 |
| 5 | 94 | 87 | 81 | 77 | 93 | 86 | 81 | 77 | 84 | 80 | 76 | 82 | 79 | 76 | 81 | 78 | 75 | 74 | 74 | 74 | 74 |
| 6 | 90 | 82 | 76 | 73 | 89 | 81 | 76 | 72 | 80 | 75 | 72 | 78 | 74 | 71 | 77 | 74 | 71 | 70 | 70 | 70 | 70 |
| 7 | 86 | 78 | 72 | 68 | 85 | 77 | 72 | 68 | 76 | 71 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 66 | 66 | 66 | 66 |
| 8 | 83 | 74 | 68 | 65 | 82 | 73 | 68 | 64 | 72 | 68 | 64 | 71 | 67 | 64 | 70 | 67 | 64 | 62 | 62 | 62 | 62 |
| 9 | 79 | 70 | 65 | 61 | 78 | 70 | 65 | 61 | 69 | 64 | 61 | 68 | 64 | 61 | 67 | 63 | 61 | 59 | 59 | 59 | 59 |
| 10 | 76 | 67 | 62 | 58 | 75 | 67 | 62 | 58 | 66 | 61 | 58 | 65 | 61 | 58 | 65 | 61 | 58 | 57 | 57 | 57 | 57 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 323702 |
| 5° | 316134 |
| 10° | 290598 |
| 15° | 246222 |
| 20° | 191047 |
| 25° | 133556 |
| 30° | 84140 |
| 35° | 49523 |
| 40° | 28024 |
| 45° | 13614 |
| 50° | 4742 |
| 55° | 3823 |
| 60° | 3728 |
| 65° | 3580 |
| 70° | 3462 |
| 75° | 3304 |
| 80° | 2904 |
| 85° | 2013 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13614 cd/sqm



TEST NUMBER: P1297453

CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DL1H_5000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 132.9 | 15.4 |
| 10°-20° | 297.9 | 34.6 |
| 20°-30° | 252.9 | 29.3 |
| 30°-40° | 120.7 | 14.0 |
| 40°-50° | 36.3 | 4.2 |
| 50°-60° | 9.2 | 1.1 |
| 60°-70° | 6.9 | 0.8 |
| 70°-80° | 4.1 | 0.5 |
| 80°-90° | 1.2 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 683.7 | 79.3 |
| 0°-40° | 804.4 | 93.3 |
| 0°-60° | 849.9 | 98.6 |
| 0°-90° | 862.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 862.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1476 | |
| 5° | 1436 | 133 |
| 15° | 1085 | 298 |
| 25° | 552 | 253 |
| 35° | 185 | 121 |
| 45° | 44 | 36 |
| 55° | 10 | 9 |
| 65° | 7 | 7 |
| 75° | 4 | 4 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P1297453
CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DL1H_5000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1476.2 |
| 2.5° | 1467.0 |
| 5° | 1436.2 |
| 7.5° | 1383.0 |
| 10° | 1305.1 |
| 12.5° | 1201.8 |
| 15° | 1084.6 |
| 17.5° | 954.4 |
| 20° | 818.7 |
| 22.5° | 680.7 |
| 25° | 552.0 |
| 27.5° | 434.8 |
| 30° | 332.3 |
| 32.5° | 249.8 |
| 35° | 185.0 |
| 37.5° | 136.4 |
| 40° | 97.9 |
| 42.5° | 67.8 |
| 45° | 43.9 |
| 47.5° | 24.7 |
| 50° | 13.9 |
| 52.5° | 10.8 |
| 55° | 10.0 |
| 57.5° | 9.3 |
| 60° | 8.5 |
| 62.5° | 7.7 |
| 65° | 6.9 |
| 67.5° | 6.2 |
| 70° | 5.4 |
| 72.5° | 4.6 |
| 75° | 3.9 |
| 77.5° | 3.1 |
| 80° | 2.3 |
| 82.5° | 1.5 |
| 85° | 0.8 |
| 87.5° | 0.8 |
| 90° | 0.0 |

(END OF REPORT)