

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297496

Luminaire Tested: P3AS13R45W2N902765DE010 E3DLD1LI_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297496
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45W2N902765DE010 E3DLD1LI_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 6500K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 669.0 lumens
Efficiency: N/A
Efficacy: 54.4 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297496
CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DLD1LI_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1297496

CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DLD1LI_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | |
| RCR | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | 100 |
| 1 | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99 | 99 | 97 | 96 | 96 | 94 | 93 | 91 | | | | 91 |
| 2 | 106 | 100 | 95 | 91 | 103 | 98 | 94 | 90 | 95 | 91 | 88 | 92 | 89 | 86 | 89 | 87 | 85 | 83 | | | | 83 |
| 3 | 99 | 92 | 86 | 82 | 97 | 90 | 85 | 81 | 88 | 83 | 80 | 85 | 81 | 78 | 83 | 80 | 77 | 75 | | | | 75 |
| 4 | 94 | 85 | 78 | 74 | 92 | 84 | 78 | 73 | 81 | 76 | 72 | 79 | 75 | 71 | 77 | 74 | 71 | 69 | | | | 69 |
| 5 | 88 | 79 | 72 | 67 | 86 | 78 | 71 | 67 | 76 | 70 | 66 | 74 | 69 | 65 | 72 | 68 | 65 | 63 | | | | 63 |
| 6 | 83 | 73 | 66 | 61 | 81 | 72 | 66 | 61 | 71 | 65 | 61 | 69 | 64 | 60 | 68 | 63 | 60 | 58 | | | | 58 |
| 7 | 78 | 68 | 61 | 57 | 77 | 67 | 61 | 56 | 66 | 60 | 56 | 65 | 60 | 56 | 64 | 59 | 55 | 54 | | | | 54 |
| 8 | 74 | 64 | 57 | 52 | 73 | 63 | 57 | 52 | 62 | 56 | 52 | 61 | 56 | 52 | 60 | 55 | 52 | 50 | | | | 50 |
| 9 | 70 | 60 | 53 | 49 | 69 | 59 | 53 | 49 | 58 | 52 | 48 | 57 | 52 | 48 | 56 | 52 | 48 | 47 | | | | 47 |
| 10 | 67 | 56 | 50 | 45 | 66 | 56 | 49 | 45 | 55 | 49 | 45 | 54 | 49 | 45 | 53 | 48 | 45 | 44 | | | | 44 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 141853 |
| 5° | 139335 |
| 10° | 131839 |
| 15° | 120250 |
| 20° | 106339 |
| 25° | 92328 |
| 30° | 79253 |
| 35° | 66040 |
| 40° | 49206 |
| 45° | 30112 |
| 50° | 13953 |
| 55° | 10896 |
| 60° | 10482 |
| 65° | 9599 |
| 70° | 8912 |
| 75° | 8472 |
| 80° | 7829 |
| 85° | 5787 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 30112 cd/sqm



TEST NUMBER: P1297496

CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DLD1LI_6500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 59.1 | 8.8 |
| 10°-20° | 147.5 | 22.0 |
| 20°-30° | 175.2 | 26.2 |
| 30°-40° | 152.2 | 22.8 |
| 40°-50° | 76.3 | 11.4 |
| 50°-60° | 26.5 | 4.0 |
| 60°-70° | 18.6 | 2.8 |
| 70°-80° | 10.4 | 1.6 |
| 80°-90° | 3.1 | 0.5 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 381.8 | 57.1 |
| 0°-40° | 534.0 | 79.8 |
| 0°-60° | 636.9 | 95.2 |
| 0°-90° | 669.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 669.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 647 | |
| 5° | 633 | 59 |
| 15° | 530 | 147 |
| 25° | 382 | 175 |
| 35° | 247 | 152 |
| 45° | 97 | 76 |
| 55° | 28 | 26 |
| 65° | 18 | 19 |
| 75° | 10 | 10 |
| 85° | 2 | 3 |
| 90° | 0 | |



TEST NUMBER: P1297496
CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DLD1LI_6500K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 646.9 |
| 2.5° | 643.8 |
| 5° | 633.0 |
| 7.5° | 616.0 |
| 10° | 592.1 |
| 12.5° | 562.8 |
| 15° | 529.7 |
| 17.5° | 492.7 |
| 20° | 455.7 |
| 22.5° | 417.9 |
| 25° | 381.6 |
| 27.5° | 346.9 |
| 30° | 313.0 |
| 32.5° | 280.6 |
| 35° | 246.7 |
| 37.5° | 210.5 |
| 40° | 171.9 |
| 42.5° | 134.2 |
| 45° | 97.1 |
| 47.5° | 64.0 |
| 50° | 40.9 |
| 52.5° | 31.6 |
| 55° | 28.5 |
| 57.5° | 26.2 |
| 60° | 23.9 |
| 62.5° | 21.6 |
| 65° | 18.5 |
| 67.5° | 16.2 |
| 70° | 13.9 |
| 72.5° | 11.6 |
| 75° | 10.0 |
| 77.5° | 7.7 |
| 80° | 6.2 |
| 82.5° | 4.6 |
| 85° | 2.3 |
| 87.5° | 1.5 |
| 90° | 0.0 |

(END OF REPORT)