

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295588

Luminaire Tested: P3AS13R15W2N902765DE010 E3DLD1MW\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1295588  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R15W2N902765DE010 E3DLD1MW\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,  
E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 602.9 lumens  
Efficiency: N/A  
Efficacy: 49.0 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295588  
CATALOG NUMBER: P3AS13R15W2N902765DE010 E3DLD1MW\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1295588  
 CATALOG NUMBER: P3AS13R15W2N902765DE010 E3DLD1MW\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91	91	91	91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83	83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76	76	76	76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65	65	65	65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60	60	60	60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56	56	56	56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	152093
5°	147964
10°	135224
15°	118434
20°	101602
25°	84827
30°	67884
35°	50915
40°	36955
45°	24158
50°	15113
55°	10208
60°	9034
65°	8302
70°	7822
75°	7117
80°	6693
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24158 cd/sqm



TEST NUMBER: P1295588

CATALOG NUMBER: P3AS13R15W2N902765DE010 E3DLD1MW\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.0	10.3
10°-20°	145.4	24.1
20°-30°	160.2	26.6
30°-40°	119.9	19.9
40°-50°	62.2	10.3
50°-60°	25.8	4.3
60°-70°	16.0	2.6
70°-80°	9.0	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	367.6	61.0
0°-40°	487.5	80.9
0°-60°	575.4	95.4
0°-90°	602.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	602.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	694	
5°	672	62
15°	522	145
25°	351	160
35°	190	120
45°	78	62
55°	27	26
65°	16	16
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1295588  
CATALOG NUMBER: P3AS13R15W2N902765DE010 E3DLD1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	693.6
1°	694.4
2°	692.1
3°	687.5
4°	680.6
5°	672.2
6°	661.5
7°	650.1
8°	636.3
9°	621.8
10°	607.3
12.5°	565.3
15°	521.7
17.5°	478.2
20°	435.4
22.5°	391.9
25°	350.6
27.5°	309.4
30°	268.1
32.5°	227.6
35°	190.2
37.5°	158.1
40°	129.1
42.5°	102.4
45°	77.9
47.5°	58.8
50°	44.3
52.5°	32.8
55°	26.7
57.5°	23.7
60°	20.6
62.5°	18.3
65°	16.0
67.5°	13.8
70°	12.2
72.5°	9.9
75°	8.4
77.5°	6.9
80°	5.3
82.5°	3.8
85°	2.3
87.5°	0.8
90°	0.0

(END OF REPORT)