

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295635

Luminaire Tested: P3AS13R15W2N902765DE010 E3DLP1WMH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1295635  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R15W2N902765DE010 E3DLP1WMH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,  
E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 427.0 lumens  
Efficiency: N/A  
Efficacy: 34.7 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295635  
CATALOG NUMBER: P3AS13R15W2N902765DE010 E3DLP1WMH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1295635

CATALOG NUMBER: P3AS13R15W2N902765DE010 E3DLP1WMH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	184130
5°	170173
10°	135869
15°	102634
20°	78150
25°	59568
30°	42665
35°	27840
40°	17061
45°	10327
50°	6857
55°	5314
60°	4561
65°	3943
70°	3526
75°	3558
80°	2652
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10327 cd/sqm



TEST NUMBER: P1295635

CATALOG NUMBER: P3AS13R15W2N902765DE010 E3DLP1WMH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.5	16.0
10°-20°	126.4	29.6
20°-30°	112.5	26.3
30°-40°	66.5	15.6
40°-50°	27.3	6.4
50°-60°	12.8	3.0
60°-70°	7.8	1.8
70°-80°	4.1	1.0
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	307.4	72.0
0°-40°	373.9	87.6
0°-60°	414.1	97.0
0°-90°	427.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	427.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	840	
5°	773	68
15°	452	126
25°	246	113
35°	104	67
45°	33	27
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1295635  
CATALOG NUMBER: P3AS13R15W2N902765DE010 E3DLP1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	839.7
1°	837.6
2°	831.4
3°	818.9
4°	798.1
5°	773.1
6°	746.1
7°	714.2
8°	680.9
9°	646.9
10°	610.2
12.5°	526.3
15°	452.1
17.5°	388.3
20°	334.9
22.5°	287.8
25°	246.2
27.5°	205.9
30°	168.5
32.5°	134.5
35°	104.0
37.5°	79.7
40°	59.6
42.5°	44.4
45°	33.3
47.5°	25.7
50°	20.1
52.5°	16.6
55°	13.9
57.5°	11.8
60°	10.4
62.5°	9.0
65°	7.6
67.5°	6.9
70°	5.5
72.5°	4.9
75°	4.2
77.5°	2.8
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)